

# Product data sheet

## Characteristics

# 70-750DL11-1

Socket, SE Relays general purpose relay accessory, 3PDT, 16A, 600 V, 11 pins, screw clamp terminal, 750/750H series



### Main

Product Range	Legacy
Product Type	Socket
Product Compatibility	Relay 750XCXR Relay 750XCXH Suppressor module 70-ASMM Diode 70-ASMD Signalling device 70-ASMLG Suppressor module 70-ASMR Jumper wire 16-750CBJ-1
Number of Terminals	11
Switch Function	3PDT
Contact Composition	3 NO + 3 NC

### Complementary

Rated Current	16 A
[Ue] rated operational voltage	300 V
Contact Terminal Arrangement	Mixed
Connections Terminals	Output screw clamp terminalssolid Output screw clamp terminalsstranded
Tightening Torque	< 1 N.m
Fixing Mode	By screw M3.5, M3.5 panel Clip-on 35 mm DIN rail
Shape of Screw Head	Combination roundhead
Product Weight	2.75 oz (78 g)
Width	1.50 in (38 mm)
Depth	3.02 in (76.81 mm)

### Environment

Ambient Air Temperature for Storage	-40...221 °F (-40...105 °C)
Ambient Air Temperature for Operation	-40...131 °F (-40...55 °C)
IP Degree of Protection	IP20
Flame Retardance	UL94-V0
Product Certifications	UL CSA CE

### Ordering and shipping details

GTIN	3606480277993
Nbr. of units in pkg.	1
Package weight(Lbs)	2.75 oz (78.0 g)

### Packing Units


Unit Type of Package 1	PCE
Package 1 Height	3.19 in (8.1 cm)
Package 1 width	1.50 in (3.8 cm)
Package 1 Length	1.46 in (3.7 cm)
Unit Type of Package 2	CAR

Number of Units in Package 2	10
Package 2 Weight	27.51 oz (780.0 g)
Package 2 Height	3.27 in (8.3 cm)
Package 2 width	2.91 in (7.4 cm)
Package 2 Length	7.64 in (19.4 cm)
Unit Type of Package 3	BB1
Number of Units in Package 3	100
Package 3 Weight	37.48 lb(US) (17.0 kg)
Package 3 Height	16.22 in (41.2 cm)
Package 3 width	9.06 in (23 cm)
Package 3 Length	16.10 in (40.9 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.


Approximate Dimensions



---

Connections and Wiring Diagrams

---



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[70-750DL11-1](#)