



## Main

Product Range	Legacy
Product Type	Socket
Product Compatibility	Relay 784XDX Suppressor module 70-ASMM Diode 70-ASMD Signalling device 70-ASMLG Suppressor module 70-ASMR
Number of Terminals	14
Switch Function	4PDT
Contact Composition	4 NO + 4 NC

## Complementary

Rated Current	16 A
[Ue] rated operational voltage	300 V
Contact Terminal Arrangement	Mixed
Connections Terminals	Output screw clamp terminalssolid Output screw clamp terminalsstranded
Tightening Torque	0.9 N.m
Fixing Mode	By screw M3.5, M3.5 panel Clip-on 35 x 15 mm symmetrical DIN rail
Shape of Screw Head	Combination roundhead
Product Weight	2.19 oz (62 g)
Width	1.97 in (50 mm)
Depth	3.13 in (79.6 mm)

## Environment

Ambient Air Temperature for Storage	-40...221 °F (-40...105 °C)
Ambient Air Temperature for Operation	-40...131 °F (-40...55 °C)
IP Degree of Protection	IP20
Flame Retardance	UL94-V0
Product Certifications	UL CSA CE

## Ordering and shipping details

GTIN	3606480278181
Nbr. of units in pkg.	1
Package weight(Lbs)	2.19 oz (62.0 g)

## Packing Units


Unit Type of Package 1	PCE
Package 1 Height	3.31 in (8.4 cm)
Package 1 width	1.97 in (5 cm)
Package 1 Length	1.18 in (3 cm)
Unit Type of Package 2	BB1

Number of Units in Package 2	10
Package 2 Weight	21.87 oz (620.0 g)
Package 2 Height	3.37 in (8.55 cm)
Package 2 width	2.42 in (6.15 cm)
Package 2 Length	9.98 in (25.35 cm)
Unit Type of Package 3	CAR
Number of Units in Package 3	200
Package 3 Weight	27.34 lb(US) (12.4 kg)
Package 3 Height	11.81 in (30 cm)
Package 3 width	13.78 in (35 cm)
Package 3 Length	17.32 in (44 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Approximate Dimensions



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[70-784D14-1](#)