



Overview

Presentation	This APC Switched Rack PDU power distribution unit has a wide range of standardized PDU features that increase network efficiency, manageability and functionality. The output and input connections are (8)5-15. Network management capabilities allow you to configure and manage rack PDUs from remote locations. It has a local current monitoring display that gives a visible warning in case of an overload. The remote individual outlet control provides real-time monitoring of connected loads. It has a multi-tier user access that enables you to restrict unauthorized use of outlets. This rack has a single input power source making it easy to install.
Lead time	Usually in Stock

General

Provided Equipment	Cord retention bracket(s) Horizontal mounting brackets User Manual Installation guide
--------------------	--

Physical

Cable length	12 Ft (3.66 m)
Color	Black
Depth	4.25 In (10.8 cm)
Height	1.73 In (4.4 cm)
Product Weight	5.00 Lb(US) (2.27 kg)
Width	17.52 In (44.5 cm)

Input

Line Rated Current	12 A
Permissible voltage	100...120 V
Input current limits	15 A
Load Capacity	1440 VA
Input Frequency	50/60 Hz
Plug standard	NEMA 5-15P
Nominal Input Voltage	100 V 120 V

Output

Number of power socket outlets	8 NEMA 5-15R
--------------------------------	--------------

Conformance

Product Certifications	CUL Listed UL Listed
Standards	FCC Part 15 class A ICES-003

Environmental

Ambient Air Temperature for Operation	32...113 °F (0...45 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 Ft (0.00...15240.00 m)






Ordering and shipping details

GTIN	00731304331568
Package weight(Lbs)	7.61 Lb(US) (3.45 kg)

Packing Units

Package 1 Height	2.76 In (7 cm)
Package 1 width	18.50 In (47 cm)
Package 1 Length	13.50 In (34.3 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Product Life Status : **Commercialised**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[AP7900B](#)