


GV2AF3

TeSys GV2, interconnection block, to connect
GV2 and LC1D09 to D38 contactor



Main

Range	Linery
Product name	FT
Device short name	GV2AF
Product or Component Type	Combination block
Accessory / separate part category	Connection accessory
Range compatibility	TeSys GV2 TeSys D TeSys TeSys Deca

Complementary

Product Compatibility	LC1D09...D38
Poles description	3P
[Ie] rated operational current	32 A
Quantity per Set	Set of 10
Net Weight	0.04 lb(US) (0.016 kg)

Ordering and shipping details

Category	22367-MANUAL STR PROTECTOR - GV2
Discount Schedule	I11
GTIN	3389110569063
Nbr. of units in pkg.	1
Package weight(Lbs)	0.78 oz (22.0 g)
Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	3.74 in (9.5 cm)
Package 1 width	3.94 in (10 cm)
Package 1 Length	5.91 in (15 cm)
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	9.45 oz (268.0 g)
Package 2 Height	3.74 in (9.5 cm)
Package 2 width	3.94 in (10 cm)
Package 2 Length	5.91 in (15 cm)
Unit Type of Package 3	P06
Number of Units in Package 3	1120
Package 3 Weight	95.51 lb(US) (43.324 kg)
Package 3 Height	30.31 in (77 cm)
Package 3 width	31.50 in (80 cm)
Package 3 Length	23.62 in (60 cm)

Offer Sustainability


Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------


GV2AF01

Combination GV2ME + TeSys k contactor




GV2AF3

Combination GV2ME + TeSys d contactor



GV2ME +	LC1D09...D18	LC1D25 and D32
b	176.4	186.8
c1	94.1	100.4
c	99.6	105.9

Combination GV2P + TeSys d contactor



GV2P +	LC1D09...D18	LC1D25 and D32
b	176.4	186.8
c1	100.1	106.4
c	105.6	111.9
d1	95	95
d	100.5	100.5

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[GV2AF3](#)