



Main

Range of product	EcoStruxure operator terminal Expert Harmony ST6
Product or component type	License
Variant	Buildtime
User language	Spanish Portuguese Italian French English Chinese German
Format	Paper
Previous software version	V3.0

Complementary

Range compatibility	Harmony STO Harmony GTU Harmony IPC Harmony ST6
Software designation	EcoStruxure Operator Terminal Expert
Type of license	Group (3 seats)
Software version	V3.1 to V3.X
Operating system	Windows 7 64 bit Windows 8.1 64 bit Windows 10 64 bit
Processor name	Intel Core i5 4th generation Intel Core i3 8th generation 8109U
Video controller type	Intel HD Graphics, 1 GB
System requirements	4 GB RAM 30 GB hard-drive space

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Communication port protocol	A series Ethernet CANopen slave CS/CJ series Ethernet CS/CJ series HOST link CS/CJ/NJ series Ethernet/IP DF1 DH485 Ethernet Modbus TCP/IP Ethernet TCP/IP EtherNet/IP Ethernet/Modbus TCP FX series CPU direct FX series Ethernet FX series computer link HTTP MELSEC MPI Modbus SIO master Modbus SIO slave Modbus TCP master Modbus TCP slave PacDrive Profibus DP slave Q CPU (SIO) Q series CPU direct Q series QnU CPU Ethernet Q/QnA Series Ethernet Q/QnA series serial QnA CPU (SIO) ROC Plus Ethernet ROC Plus SIO Simatic S7 Ethernet Simatic S7 MPI direct SoMachine network TIA portal Ethernet Zelio Logic IQ-R/F series Ethernet
Software function	Basic screen design and function Security feature Alarm feature Sampling and trending feature Blocky function Web viewer (additional runtime license) Web API OPC UA server

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	55 G
Package 1 Height	0.15 Cm
Package 1 width	18 Cm
Package 1 Length	25 Cm
Unit Type of Package 2	S02
Number of Units in Package 2	8
Package 2 Weight	440 G
Package 2 Height	15 Cm
Package 2 width	30 Cm
Package 2 Length	40 Cm

Product Life Status : **Commercialised**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Schneider Electric:

HMIPELCZLGPMZZ