

Product data sheet

Characteristics

P6M10

APC Essential SurgeArrest, 6 outlets, 10ft cord, metal housing, 120V



Commercial status

This Product is Obsolete : JUL 08, 2021

⚠ This Product is Obsolete

Overview

Lead time	Usually in Stock
-----------	------------------

Physical

Cable length	10 Ft (3.05 m)
Color	Gray
Depth	1.50 In (3.8 cm)
Height	12.24 In (31.1 cm)
Product Weight	1.54 Lb(US) (0.7 kg)
Width	2.48 In (6.3 cm)

Input

Input power	1875 W
Input Frequency	50/60 Hz +/- 3 Hz auto-sensing
Plug standard	NEMA 5-15P
Maximum Input Current per Phase	15 A
Switching current capacity	15 A
Nominal Input Voltage	120 V

Output

Number of power socket outlets	6
Outlet standard	NEMA 5-15R

Conformance

UL 1449 TVSS Rating	330
Equipment protection policy	Lifetime : \$25000

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...50000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 Ft (0.00...15240.00 m)

Surge Protection and Filtering

Surge energy rating	540 J
---------------------	-------

Ordering and shipping details

GTIN	00731304253204
Package weight(Lbs)	1.76 Lb(US) (0.8 kg)

Packing Units

Package 1 Height	13.19 In (33.5 cm)
Package 1 width	3.94 In (10 cm)
Package 1 Length	45.98 In (116.8 cm)
SCC14	10731304253201
Number of Units in Package 2	12
Package 2 Weight	24.2 Lb(US) (10.98 kg)
Package 2 Height	12.75 In (323.85 mm)
Package 2 width	9 In (228.60 mm)
Package 2 Length	15.5 In (393.70 mm)
Number of Units in Package 3	288

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: 1,3-Butadiene, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	Limited Lifetime
----------	------------------

Product Life Status : **End of commercialisation**

P6M10 may be replaced by any of the following products:



PE615
APC Essential SurgeArrest 6 Outlet 15 Foot Cord 120V
Qty 1
Substitution date: |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[P6M10](#)