

Product data sheet

Characteristics

P6TM

APC Essential SurgeArrest 6 Outlets with Phone Protection 120V Metal



Commercial status

This Product is Obsolete : SEP 01, 2021

⚠ This Product is Obsolete

Overview

Lead time	Usually in Stock
-----------	------------------

General

Provided equipment	Telephone cable
--------------------	-----------------

Physical

Cable length	4 Ft (1.22 m)
Color	Gray
Depth	1.50 In (3.8 cm)
Height	12.24 In (31.1 cm)
Product Weight	1.54 Lb(US) (0.7 kg)
Width	2.48 In (6.3 cm)

Input

Input power	1875 W
Input Frequency	50/60 Hz +/- 3 Hz auto-sensing
Plug standard	NEMA 5-15P
Maximum Input Current per Phase	15 A
Switching current capacity	15 A
Nominal Input Voltage	120 V

Output

Number of power socket outlets	6
Outlet standard	NEMA 5-15R

Conformance

UL 1449 TVSS Rating	330
Equipment protection policy	Lifetime : \$25000

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...50000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 Ft (0.00...15240.00 m)

Surge Protection and Filtering

Surge energy rating	540 J
Data line protection	RJ11 Modem/Fax protection

Ordering and shipping details

Category	11309 - APC RESALE PRODUCTS
GTIN	00731304248262
Nbr. of units in pkg.	1
Package weight(Lbs)	1 Lb(US) (0.45 kg)
Returnability	No
Country of origin	TW

Packing Units

Package 1 Height	13.19 In (33.5 cm)
Package 1 width	3.94 In (10 cm)
Package 1 Length	45.98 In (116.8 cm)
SCC14	10731304248269
Number of Units in Package 2	12
Package 2 Weight	24.2 Lb(US) (10.98 kg)
Package 2 Height	12.75 In (323.85 mm)
Package 2 width	9 In (228.60 mm)
Package 2 Length	15.5 In (393.70 mm)
Number of Units in Package 3	288

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: 1,3-Butadiene, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	Limited Lifetime
----------	------------------

Product Life Status : Post commercialisation

P6TM is replaced by the following product range:



61875
Professional-grade Electrical Surge Protection for Computers and Electronics
Substitution date: |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[P6TM](#)