

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range of product	Harmony XVB Universal
Product or component type	Complete beacon
Beacon or indicator bank unit type	Base unit with direct or tube fixing mode Illuminated unit
Signalling type	Flashing
Mounting diameter	2.76 in (70 mm)
Component name	XVBL
Material	Glass reinforced polyamide (base unit) Polycarbonate (illuminated unit)
Light source	Blue integral flash discharge tube
Bulb type	Flash discharge tube
[Us] rated supply voltage	24 V AC/DC

Complementary

Connections - terminals	Screw clamp terminals, connection capacity: $\leq 1 \times 1.5 \text{ mm}^2$ with cable end
[Ui] rated insulation voltage	250 V conforming to IEC 60947-1
Nominal voltage limit	0.85...1.1 U_n conforming to IEC 60947-5-1
Current consumption	< 350 mA DC < 550 mA AC
[Uimp] rated impulse withstand voltage	4 kV conforming to IEC 60947-1
Flash energy	5 J
Flashing frequency	1 Hz
CAD overall width	2.76 in (70 mm)
CAD overall height	9.13 in (232 mm)
CAD overall depth	2.76 in (70 mm)
Terminals description ISO n°1	(COM-1)PW (GND)GROUND
Product weight	0.97 lb(US) (0.44 kg)

Environment

Product certifications	CSA C22-2 No 14 CCC UL 508 GOST
Standards	EN/IEC 60947-5-1
Protective treatment	TC
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Electrical shock protection class	Class I (on support tube) conforming to IEC 61140 Class II (on base unit) conforming to IEC 61140
IP degree of protection	IP65 (on fixing base XVBZ0.) conforming to IEC 60529 IP66 (on base unit) conforming to IEC 60529
NEMA degree of protection	NEMA 4X (indoor) conforming to UL 508

Ordering and shipping details

Category	22611 - XVB-STACKLIGHTS
Discount Schedule	XV
GTIN	003389110844696
Nbr. of units in pkg.	1
Package weight(Lbs)	0.9699999999999997
Returnability	N
Country of origin	CZ

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Illuminated Beacon with “Flash” Discharge Tube Unit

Dimensions



Illuminated Beacon

Wiring Diagram



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XVBL6B6](#)