

Product data sheet

Specifications



Rack PDU, Metered, 1U, 12A/208V, 10A/230V, (8) C13



AP7820

- ⚠ Discontinued on: 11 March 2022
- ⚠ To be end-of-service on: 28 June 2023

⚠ Discontinued - Service only

Overview

Lead time Usually in Stock

Main

Main Input Voltage	200 V 208 V 230 V
Main Output Voltage	208 V 230 V
Plug standard	IEC 60320 C14
Number of rack unit	1U
Cable length	6.5 ft (1.98 m)
Provided equipment	Cord retention bracket(s) Installation guide Rack Mounting brackets User Manual

Physical

Height	1.73 in (4.4 cm)
Width	17.48 in (44.4 cm)
Depth	4.02 in (10.2 cm)
Net Weight	3.81 lb(US) (1.73 kg)
Mounting Location	Front Rear
Mounting preference	No preference
Mounting Mode	Rack-mounted

Input

Line Rated Current	10 A
Input current limits	15 A
Load Capacity	2300 VA
Input Frequency	50/60 Hz

Output

Different voltages and corresponding amperages	10 A - 230 V 12 A - 208 V
Number of power socket outlets	8 IEC 60320 C13

Conformance

Product certifications	cUL Listed C-tick CE CSA GOST UL Listed VDE VCCI
Standards	FCC Part 15 class A UL 60950

Environmental

Ambient Air Temperature for Operation	23...113 °F (-5...45 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

GTIN	00731304246596
Package weight(Lbs)	6.42 lb(US) (2.91 kg)

Packing Units

Package 1 Height	2.52 in (6.4 cm)
Package 1 width	18.50 in (47 cm)
Package 1 Length	13.27 in (33.7 cm)

Offer Sustainability


Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Lead free	Yes
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Recommended replacement(s)

AP7820 is replaced by:

1x		Rack PDU, Metered, 1U, 12A/208V, 10A/230V, (8) C13 AP7820B
----	---	---

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[AP7820](#)