

XSDN401229

Inductive proximity sensors XS, inductive sensor XSD, form D flat, Sn 40 mm, screw clamp terminals



Main

Range of product	Telemecanique Inductive proximity sensors XS
Series name	General purpose
Sensor type	Inductive proximity sensor
Sensor name	XSD
Sensor design	Form 80 x 80 x 40
Size	40 mm
Body type	Fixed
Enclosure material	Plastic
Type of output signal	Discrete
Wiring technique	2-wire
Discrete output function	1 NO or 1 NC programmable
Electrical connection	Screw-clamp terminals
[Us] rated supply voltage	12...240 V
IP degree of protection	IP67

Complementary

Detection face	Frontal
Detector flush mounting acceptance	Non flush mountable
Material	Plastic
Front material	Plastic
Switching capacity in mA	5...100 mA DC 5...500 mA AC
Switching frequency	≤ 10 Hz
Marking	CE
Depth	1.57 in (40 mm)
Height	3.94 in (100 mm)
Width	3.15 in (80 mm)

Environment

Product certifications	CCC
------------------------	-----

Ordering and shipping details

Category	22486 - SENSORS, PROXIMITY
Discount Schedule	DS2
GTIN	00785901603597
Nbr. of units in pkg.	1
Package weight(Lbs)	1.06 lb(US) (0.48 kg)
Returnability	No
Country of origin	FR

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the company. This information is not intended to be used as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.17 in (5.5 cm)
Package 1 width	3.54 in (9 cm)
Package 1 Length	5.91 in (15 cm)
Unit Type of Package 2	S02
Number of Units in Package 2	11
Package 2 Weight	12.39 lb(US) (5.62 kg)
Package 2 Height	5.91 in (15 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XSDN401229](#)