

Product data sheet

Characteristics

P8GT

APC Power-Saving Home/Office SurgeArrest, 8 Outlets with Phone Protection, 120V



Overview

Lead time	Usually in Stock
-----------	------------------

General

Provided equipment	Telephone cable User manual
--------------------	--------------------------------

Physical

Cable length	6 Ft (1.83 m)
Color	White
Depth	1.50 In (3.8 cm)
Height	10.51 In (26.7 cm)
Product Weight	1.21 Lb(US) (0.55 kg)
Width	4.80 In (12.2 cm)

Input

Input Frequency	50/60 Hz
Plug standard	NEMA 5-15P
Maximum Input Current per Phase	15 A
Nominal Input Voltage	120 V

Output

Number of power socket outlets	8
Outlet standard	NEMA 5-15R

Conformance

UL 1449 TVSS Rating	400
Product Certifications	ETL
Standards	UL 1449
Equipment protection policy	Lifetime : \$150000

Environmental

Ambient Air Temperature for Operation	32...113 °F (0...45 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	23...113 °F (-5...45 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 Ft (0.00...15240.00 m)

Surge Protection and Filtering

NM Surge Response Time (ns)	1 ns common mode
Common mode rejection	58 DB
Peak current	144 KA common mode
Surge energy rating	2160 J
Data line protection	RJ11 Modem/Fax protection (two wire single line)

Ordering and shipping details

GTIN	00731304269229
Package weight(Lbs)	2.12 Lb(US) (0.96 kg)

Packing Units

Package 1 Height	14.25 In (36.2 cm)
Package 1 width	9.76 In (24.8 cm)
Package 1 Length	1.73 In (4.4 cm)
SCC14	10731304269226
Number of Units in Package 2	6
Package 2 Weight	15.79 Lb(US) (7.16 kg)
Package 2 Height	16.3 In (414.02 mm)
Package 2 width	12.87 In (326.90 mm)
Package 2 Length	14.6 In (370.84 mm)
Number of Units in Package 3	216

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: 1,3-Butadiene, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	Lifetime
----------	----------

Product Life Status : **Commercialised**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[P8GT](#)