



Overview

Lead time	Usually Ships within 8 Weeks
-----------	------------------------------



Main

Main Input Voltage	120 V
Plug standard	NEMA 5-15P
Cable length	8 ft (2.44 m)
Number of cables	1
Provided equipment	User Manual

Physical

Color	Yellow
Height	14.96 in (38 cm)
Width	2.76 in (7 cm)
Depth	1.77 in (4.5 cm)
Net Weight	1.59 lb(US) (0.72 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Maximum Line Current per phase	15 A
Input Frequency	50/60 Hz +/- 5 Hz auto-sensing

Output

Number of power socket outlets	7
Outlet standard	NEMA 5-15R

Conformance

UL 1449 TVSS Rating	330
Product Certifications	CSA
Standards	UL 1449
Equipment protection policy	Lifetime : \$5000

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Surge Protection and Filtering

EP Joule Rating	820 J
NM Surge Response Time (ns)	0 ns common mode
Common mode rejection	20 dB
Peak current	12 KA common mode 6 kA normal mode
Surge energy rating	800 J

Ordering and shipping details

GTIN	731304238324
Package weight(Lbs)	1.10 lb(US) (0.5 kg)

Packing Units

Package 1 Height	14.96 in (38 cm)
Package 1 width	4.29 in (10.9 cm)
Package 1 Length	2.01 in (5.1 cm)
SCC14	10731304238321
Number of Units in Package 2	12
Package 2 Weight	22.22 lb(US) (10.08 kg)
Package 2 Height	6 in (152.40 mm)
Package 2 width	13 in (330.20 mm)
Package 2 Length	31 in (787.40 mm)
Number of Units in Package 3	180

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: 1,3-Butadiene, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information

Contractual warranty

Warranty	Limited Lifetime
----------	------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[PDIY7](#)