

Product data sheet

Characteristics

PNOTEPROC8

APC Notebook Surge Protector for AC, phone and network lines, 2 pin connection, 100-240V



Commercial status

This Product is Obsolete : SEP 01, 2021

⚠ This Product is Obsolete

Overview

Lead time	Usually in Stock
-----------	------------------

General

Provided equipment	2 x 1.8 Meter Tel cable 30 cm network patch cable Cord management straps User manual
--------------------	---

Physical

Color	Silver
Depth	3.86 In (9.8 cm)
Height	1.06 In (2.7 cm)
Product Weight	0.22 Lb(US) (0.1 kg)
Width	1.26 In (3.2 cm)

Input

Input power	300 W
Maximum Line Current per phase	4 A
Input Frequency	50/60 Hz
Plug standard	IEC 60320 C8
Nominal Input Voltage	120 V

Output

Number of power socket outlets	1
Outlet standard	IEC 60320 C8

Conformance

UL 1449 TVSS Rating	700
Product Certifications	CSA NOM UL Listed
Standards	FCC part 68
Equipment protection policy	Lifetime : \$75000

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...30000 Ft (0.00...9144.00 m)

Surge Protection and Filtering

NM Surge Response Time (ns)	1 ns common mode
Common mode rejection	0 DB
Peak current	0 KA common mode 6.5 KA normal mode
Surge energy rating	180 J
Data line protection	RJ11 Modem/Fax protection (two wire single line) RJ45 10/100 Base-T Ethernet protection

Ordering and shipping details

Category	11309 - APC RESALE PRODUCTS
GTIN	00731304220725
Nbr. of units in pkg.	1
Package weight(Lbs)	1 Lb(US) (0.45 kg)
Returnability	No

Packing Units

Package 1 Height	2.60 In (6.6 cm)
Package 1 width	6.22 In (15.8 cm)
Package 1 Length	7.56 In (19.2 cm)
SCC14	10731304220722
Number of Units in Package 2	12
Package 2 Weight	6 Lb(US) (2.72 kg)
Package 2 Height	8.3 In (210.82 mm)
Package 2 width	11.5 In (292.10 mm)
Package 2 Length	16.5 In (419.10 mm)
Number of Units in Package 3	480

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	Limited Lifetime
----------	------------------

Product Life Status :	Post commercialisation
-----------------------	------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[PNOTEPROC8](#)