

Product data sheet

Specifications



APC NetShelter SX, Server Rack Enclosure, 42U, Shock Packaging, 2000 lbs, Black, 1991H x 750W x 1070D mm

AR3150SP2

⚠ Discontinued

⚠ Discontinued on: 23 August 2021

⚠ End-of-service on: 08 October 2021

Overview

Presentation	Wide enclosure with increased cable management options for high density server and networking applications. 42U height to easily roll through doorways. Additional shock packaging for shipping equipment weighing up to 2000lbs/909kg.
Lead time	Special Order - Call for Quoted Lead Times

Main

Number of rack unit	42U
Provided equipment	Baying hardware Key(s) Keyed-alike doors and side panels Leveling feet Mounting Hardware Pre-installed casters Reusable 2000lb. shock packaging Side Panels

Physical

Color	Black
Height	78.39 in (199.1 cm)
Width	29.53 in (75 cm)
Depth	42.13 in (107 cm)
Net Weight	343.81 lb(US) (155.95 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	36.02 in (91.49 cm)
Minimum Mounting Depth	10.31 in (26.19 cm)
Rack Width	19"
Marking	14 gauge EIA mounting rail 16 gauge front door 16 gauge post 16 gauge rear door 18 gauge roof 18 gauge side panels
Permanent permissible load	2250 lb(US) (1020.58 kg) dynamic 3000 lb(US) (1360.78 kg) static

Conformance

Standards	UL 60950 EIA-310E
-----------	----------------------

Ordering and shipping details

GTIN	00731304244417
Package weight(Lbs)	444.03 lb(US) (201.41 kg)

Packing Units

Package 1 Height	83.39 in (211.8 cm)
Package 1 width	45.98 in (116.8 cm)
Package 1 Length	47.99 in (121.9 cm)
Number of Units in Package 3	1

Offer Sustainability


Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
Take-back	Take-back program available

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------

Recommended replacement(s)

AR3150SP2 is replaced by:

1x		APC NetShelter SX, Server Rack Enclosure, 42U, Shock Packaging, 2000 lbs, Black, 2124H x 750W x 1070D mm AR3150SP
----	---	--

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[AR3150SP2](#)