

# Product data sheet

Specifications



## APC AV J Type 1.5kVA Power Conditioner with Battery Backup & AVR 120V

J35B

⚠ Discontinued on: 06 December 2021

⚠ End-of-service on: 06 December 2021

⚠ Discontinued - Service only

### Overview

Lead time Usually in Stock

### General

Provided equipment CD with software  
User manual

### Physical

Colour Black

Depth 40.64 cm

Height 9.76 cm

Net weight 14 kg

Width 43.18 cm

### Input

Plug standard NEMA 5-15P

Input voltage 120 V

### Output

Rated power in W 865 W

Maximum configurable power in W 865 W

Wave type Stepped approximation to a sinewave

Nb of power socket outlets 6 NEMA 5-15R  
2 NEMA 5-15R surge

Output voltage 120 V

### Conformance

Standards FCC part 15 class B  
UL 1778

Equipment protection policy Lifetime : \$350000

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-15...40 °C
Storage Relative Humidity	0...95 %
Storage altitude	0.00...3048.00 m
Acoustic level	45 dBA

Batteries & Runtime

Battery type	Lead-acid battery
Number of battery filled slots	1
Number of battery free slots	0
Battery recharge time	16 h
Liquid value	0

Surge Protection and Filtering

Surge energy rate	345 J
-------------------	-------

Packing Units

Package 1 Weight	16 kg
Package 1 Height	20.51 cm
Package 1 width	55.88 cm
Package 1 Length	53.94 cm
SCC14	10731304277696
Number of Units in Package 2	2
Package 2 Weight	33.99 kg
Package 2 Height	431.80 mm
Package 2 width	584.20 mm
Package 2 Length	558.80 mm

Offer Sustainability

EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
Optimized Energy Efficiency	Energy efficient product

Contractual warranty

Warranty	3 years repair or replace
----------	---------------------------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[J35B](#)