

Main

Device short name	G
Enclosure type	Standard environment enclosure indoor
Factory modification	2-way pressure release valve
Product Specific Application	Control electrically driven water pumps and air compressors
Range of Product	Square D Pumptrol
Switch application	Standard

Complementary

Adjustable range on rising pressure	20...80 psi (137.90...551.58 kPa)
Approximate adjustable differential	15...30 psi (103.42...206.84 kPa)
Depth	3.68 in (93.47 mm)
Electrical connection	Screw clamp terminal
Fixing Mode	By brackets
Fluid connection type	0.125 inch NPSF internal
Height	5.72 in (145.29 mm)
Material	Zinc plated steel flange
Materials in contact with fluid	Nitrile (Buna-N) diaphragm
Maximum pressure	300 psig
Maximum Horse Power Rating	2 Hp 115 V AC, 1 phase 3 Hp 115 V AC, 3 phase 3 Hp 230 V AC, 1 phase 5 Hp 230 V AC, 3 phase 5 Hp 460/575 V AC, 1 phase 5 hp 460/575 V AC, 3 phase
Number of poles	2
Permissible voltage	575 V AC
Pressure actuator	Diaphragm
Pressure setting range	60...80 psi (413.69...551.58 kPa)
Net Weight	2.25 lb(US) (1.02 kg)
Range on decreasing pressure	5...60 psi (34.47...413.69 kPa)
Scale type	Adjustable differential
Switch function	DPST
Width	3.44 in (87.38 mm)

Environment

NEMA degree of protection	NEMA 1
Product Certifications	UL listed file E12158 CCN NKPZ CSA file LR25490

Ordering and shipping details

Category	21536 - 9013 G COMMERCIAL PRESSURE SWITCH
Discount Schedule	CP7G
GTIN	785901437697
Nbr. of units in pkg.	1
Package weight(Lbs)	32.00 oz (907.185 g)
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	10.16 in (25.806 cm)
Package 1 width	4.00 in (10.16 cm)
Package 1 Length	25.81 in (65.548 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[9013GSG1J25X](#)