

Product data sheet

Characteristics

P7T

APC Essential SurgeArrest, 7 outlet, phone line protection



Commercial status

This Product is Obsolete : JUL 16, 2021

 This Product is Obsolete

Overview

Lead time	Usually in Stock
-----------	------------------

Main

Nominal Input Voltage	120 V
Plug standard	NEMA 5-15P
Cable length	6 Ft (1.83 m)
Number of cables	1
Provided equipment	2 x 1.8 Meter Tel cable User Manual

Physical

Color	Charcoal
Height	12.52 In (31.8 cm)
Width	2.99 In (7.6 cm)
Depth	1.42 In (3.6 cm)
Net Weight	1.41 Lb(US) (0.64 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Maximum Line Current per phase	15 A
Input Frequency	50/60 Hz +/- 5 Hz auto-sensing

Output

Number of power socket outlets	7
Outlet standard	NEMA 5-15R

Conformance

UL 1449 TVSS Rating	330
Product certifications	CSA
Standards	UL 1363 UL 1449
Equipment protection policy	Lifetime : \$25000

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 Ft (0.00...15240.00 m)

Surge Protection and Filtering

NM Surge Response Time (ns)	0 ns common mode
Common mode rejection	20 DB
Peak current	30 KA common mode 10 KA normal mode
Surge energy rating	840 J
Data line protection	RJ11 Modem/Fax/DSL protection (two wire single line)

Ordering and shipping details

GTIN	00731304200727
Package weight(Lbs)	1.70 Lb(US) (0.77 kg)

Packing Units

Package 1 Height	13.90 In (35.3 cm)
Package 1 width	5.24 In (13.3 cm)
Package 1 Length	1.54 In (3.9 cm)
SCC14	10731304200724
Number of Units in Package 2	12
Package 2 Weight	21.4 Lb(US) (9.71 kg)
Package 2 Length	16.25 In (412.75 mm)
Number of Units in Package 3	288

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	Limited Lifetime
----------	------------------

Product Life Status : **End of commercialisation**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[P7T](#)