



Overview

Presentation	Free up space and secure power cords between rack-mount PDUs and attached IT equipment with this exclusive easy-to-use cord retention method. While these cords will fit into any standard IEC receptacle or power inlet; the "locking" feature is enabled only when used with APC AP8000 series Rack PDUs or IT equipment with built-in locking receptacles. These locking connectors reduce the probability of accidentally disconnecting cords and dropping loads.
Lead time	Usually in Stock

Main

Main Output Voltage	120 V
Input Connection Type	NEMA L5-20P
Cable length	9.84 ft (3.00 m)
Number of cables	1

Physical

Color	Black
Height	9.06 in (23 cm)
Width	9.06 in (23 cm)
Depth	1.77 in (4.5 cm)
Net Weight	1.59 lb(US) (0.72 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Max line current	20 A
Input current limits	20 A

Output

Maximum Total Current Draw per Phase	20 A
Number of power socket outlets	1 IEC 60320 C19
Cord Length	10 ft (3.05 m)

Conformance

Product Certifications	CSA UL Listed
------------------------	------------------

Environmental

Ambient Air Temperature for Operation	32...221 °F (0...105 °C)
Relative Humidity	20...80 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...221 °F (-25...105 °C)
Storage Relative Humidity	20...80 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

Category	11309-APC RESALE PRODUCTS
Discount Schedule	APC1
GTIN	731304279754
Returnability	No
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.06 in (23 cm)
Package 1 Width	1.77 in (4.5 cm)
Package 1 Length	9.06 in (23 cm)
Package 1 Weight	1.59 lb(US) (0.72 kg)
Number of Units in Package 3	750
SCC14	10731304279751

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Lead free	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[AP8752](#)