

APCRBC109

APC Replacement Battery Cartridge #109 with 2 Year Warranty



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Product or Component Type	Replacement battery cartridge
Battery Type	Lead-Acid battery
Provided Equipment	All required connectors Battery recycling guide Reusable packaging Installation guide

Physical

Color	Charcoal
Height	4.09 in (10.4 cm)
Width	5.94 in (15.1 cm)
Depth	5.20 in (13.2 cm)
Net Weight	12.30 lb(US) (5.58 kg)
Mounting Mode	Not rack-mountable

Output

Battery Capacity	9.0 Ah
------------------	--------

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Operating altitude	0...10000 ft
Relative Humidity	0...95 %
Ambient Air Temperature for Storage	32...104 °F (0...40 °C)
Storage altitude	0...10000 ft (0.00...3048.00 m)
Storage Relative Humidity	0...95 %

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Batteries & Runtime

Battery blocks per string	2
Battery Slots Empty	0
Included Battery Modules	0
Device mounting	Enclosed battery cartridge
Battery Voltage	24 V
RBC Quantity	1

Ordering and shipping details

GTIN	731304243564
------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12.01 in (30.5 cm)
Package 1 Width	4.02 in (10.2 cm)
Package 1 Length	9.02 in (22.9 cm)
Package 1 Weight	13.54 lb(US) (6.14 kg)
SCC14	10731304243561

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[APCRBC109](#)