



Overview

| | |
|--------------|---|
| Presentation | An industry standard rack with the most standard features for speed of deployment and installation. Ready for low to medium density edge computing. Shorter height allows for deployment underneath cabinets, desks, in remote office branch office spaces for a secure and discrete solution for IT devices. |
| Lead time | Usually in Stock |

Main

| | |
|---------------------------|--|
| Product or Component Type | Rack enclosure |
| Number of rack unit | 12U |
| Provided equipment | Casters Doors Key(S) Leveling feet Roof Side Panels |

Physical

| | |
|----------------------------|---|
| Height | 25.91 in (65.8 cm) |
| Width | 23.62 in (60 cm) |
| Depth | 35.43 in (90 cm) |
| Net Weight | 119.01 lb(US) (53.98 kg) |
| Color | Black |
| Mounting preference | No preference |
| Mounting Mode | Not rack-mountable |
| Maximum Mounting Depth | 29.75 in (75.57 cm) |
| Minimum Mounting Depth | 7.52 in (19.1 cm) |
| Rack width | 19" |
| Marking | 14 gauge EIA mounting rail 16 gauge front door 16 gauge post 18 gauge rear door 18 gauge roof 18 gauge side panels |
| Permanent permissible load | 600 Lb(US) (272.16 kg) dynamic 600 lb(US) (272.16 kg) static |

Conformance

| | |
|-----------|-----------------------------------|
| Standards | UL 2416 UL 60950-1 EIA-310E |
|-----------|-----------------------------------|



Ordering and shipping details

| | |
|------|--------------|
| GTIN | 731304347507 |
|------|--------------|

Packing Units

| | |
|------------------------------|-----------------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 31.30 in (79.5 cm) |
| Package 1 Width | 39.17 in (99.5 cm) |
| Package 1 Length | 29.53 in (75 cm) |
| Package 1 Weight | 165.35 lb(US) (75 kg) |

Offer Sustainability

| | |
|-----------------------------|--|
| Sustainable offer status | Green Premium product |
| REACH Regulation |  REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration |
| Optimized Energy Efficiency | Energy efficient product |
| Take-back | Take-back program available |

Contractual warranty

| | |
|----------|--------------------------|
| Warranty | 5 year repair or replace |
|----------|--------------------------|

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[AR3003](#)