




Main

Range of Product	Preventa Safety automation
Accessory / Separate Part Type	Connecting cable
Accessory / separate part category	Cabling accessory
Accessory / separate part destination	RS485 safe communication expansion module

Complementary

Product Compatibility	XPSMCMCO0000S...
Cable length	32.81 ft (10 m)
Electrical connection	Flying leads
AWG Gauge	AWG 24
Cable insulation material	PE (polyethylene)
Type of cable	Twisted pair white/blue Twisted pair orange/white
Cable shielding type	S/FTP
[Ue] rated operational voltage	300 Vrms
Permissible current	2.1 A
Cable capacitance	0.0419 NF between two conductors) 0.07544 nF between conductor and shield)
Attenuation	1.97 dB
Nominal velocity propagation	66 %
Delay skew	1.54 ns
Insulation resistance	24 MOhm nominal conductor DC resistance 2.2 MOhm nominal outer shield DC resistance
Net Weight	2.03 lb(US) (0.92 kg)

Environment

Ambient Air Temperature for Operation	-4...176 °F (-20...80 °C)
---------------------------------------	---------------------------

Ordering and shipping details

Category	22477-SAFETY MODULES (PREVENTA)
Discount Schedule	SAF2
GTIN	3606480795916
Nbr. of units in pkg.	1
Package weight(Lbs)	24.44 oz (692.9 g)
Returnability	No
Country of origin	CZ

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.77 in (4.5 cm)
Package 1 width	8.27 in (21 cm)
Package 1 Length	8.27 in (21 cm)
Unit Type of Package 2	S02
Number of Units in Package 2	3
Package 2 Weight	5.63 lb(US) (2.553 kg)
Package 2 Height	5.91 in (15 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[TSXSCMCN010](#)