

GV2APN01

Extended rotary handle kit, TeSys GV2, IP54, black handle, with trip indication, for GV2L-GV2P



Main

Range	TeSys
Device short name	GV2AP
Product or component type	Rotary handle kit
Accessory / separate part category	Control accessory
Handle colour	Black
Handle front plate colour	Grey

Complementary

Product compatibility	GV2P GV2L
Rotary handle padlocking	Padlock in OFF position Padlock in ON position
Rotary handle mounting style	Extended
Locking options description	1 to 3 padlocks
Back/door distance	5.51...9.84 in (140...250 mm)
Net Weight	0.44 lb(US) (0.2 kg)

Environment

IP degree of protection	IP54
-------------------------	------

Ordering and shipping details

Category	22367 - MANUAL STR PROTECTOR - GV2
Discount Schedule	I11
GTIN	00785901978923
Nbr. of units in pkg.	1
Package weight(Lbs)	0.79 lb(US) (0.36 kg)
Returnability	Yes
Country of origin	CZ

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.56 in (6.5 cm)
Package 1 width	3.54 in (9 cm)
Package 1 Length	14.57 in (37 cm)
Unit Type of Package 2	S03
Number of Units in Package 2	12
Package 2 Weight	10.42 lb(US) (4.728 kg)
Package 2 Height	11.81 in (30 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)

Unit Type of Package 3	P06
Number of Units in Package 3	96
Package 3 Weight	111.32 lb(US) (50.492 kg)
Package 3 Height	31.50 in (80 cm)
Package 3 width	31.50 in (80 cm)
Package 3 Length	23.62 in (60 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------

Technical drawing of the 1000 series piezo actuator. The side view shows a cylindrical piezo actuator with a diameter of 60 mm and a length of 43 mm. It is connected to a piezo stack with a length of 0.5...4 mm. The piezo stack is connected to a piezo amplifier with a length of 6 mm. The total length of the assembly is labeled as 'a'. The front view shows a square piezo stack with a side length of 5.2 mm and a central circular hole with a diameter of 1.5 mm. The piezo stack is connected to a piezo amplifier with a length of 6 mm.

Life Is On | Schneider Electric

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[GV2APN01](#)