



Main

Range of Product	Vijeo Designer
Product or Component Type	Configuration software
User Language	Chinese Italian English German Portuguese French Spanish
Format	DVD-ROM
Previous software version	V6.1
Type of License	Single (1 station)
Software Version	V6.2

Complementary

Product Compatibility	SoMachine V4.1 or higher
Range compatibility	Harmony XBT GK Harmony STO & STU Harmony XBT GT Harmony Compact iPC Harmony GTU Harmony iPC Harmony XBT GH Harmony GTO Harmony Smart Harmony XBT GTW
Software Designation	Vijeo Designer
System requirements	Processor suitable for operating system Windows 7 Professional 32/64 bit Processor suitable for operating system Windows 8.1 Processor suitable for operating system Windows 10 Professional 32/64 bit
Communication port protocol	Profibus DP UniTE TCP/IP Fipio/Fipway USB Modbus TCP master Modbus RTU master ELAU PacDrive MELSEC Simatic Modbus 32-bit extensions ROC Plus Sysmacway Allen-Bradley Uni-Telway Toyopuc PC3J Ethernet/IP Explicit Modbus Plus
Provided Equipment	Acrobat Reader 1 cable USB Tutorial in flash format Vijeo Designer software User's documentation in electronic format
Software Function	4 asian alphabets 2 middle eastern alphabets 9999 alarms 8000 variables 34 western alphabets Sharing up to 300 variables
Audio video coding standard	JPEG

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Ordering and shipping details

Category	22569-MAGELIS XBT-GT (AND XBT-G)
Discount Schedule	MC2
GTIN	3606480712852
Nbr. of units in pkg.	1
Package weight(Lbs)	10.76 oz (305.0 g)
Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.57 in (4 cm)
Package 1 width	5.51 in (14 cm)
Package 1 Length	6.50 in (16.5 cm)
Unit Type of Package 2	S02
Number of Units in Package 2	12
Package 2 Weight	9.26 lb(US) (4.2 kg)
Package 2 Height	5.91 in (15 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[VJDSUDTGAV62M](#)