

# 9007HA5

limit switch lever arm, 9007C, bendable  
adjustable lever arm, 0.625 inch diameter  
roller, 0.25 inch wide roller



Product availability: Stock - Normally stocked in distribution facility



## Main

|                             |                                                                                            |
|-----------------------------|--------------------------------------------------------------------------------------------|
| Range of product            | 9007                                                                                       |
| Series name                 | Heavy duty                                                                                 |
| Product or component type   | Limit switch lever                                                                         |
| Device short name           | 9007C                                                                                      |
| Associated head             | 9007N<br>9007T10<br>9007B<br>9007A<br>9007C<br>9007T5                                      |
| Associated complete product | 9007AW<br>9007C                                                                            |
| Movement of operating head  | Rotary                                                                                     |
| Type of operator            | Cast zinc spring return adjustable bendable roller lever length: 0.88...4 in - offset: - - |
| Type of roller              | 1 steel outside roller diameter: 0.63 in - width: 0.25 in                                  |
| Type of approach            | Lateral approach                                                                           |
| Positive opening            | Without                                                                                    |

## Complementary

|                  |            |
|------------------|------------|
| Switch actuation | By 30° cam |
| Product weight   | 0.1 lb(US) |

## Environment

|                                       |                      |
|---------------------------------------|----------------------|
| Ambient air temperature for operation | -20...185 °F         |
| Ambient air temperature for storage   | -20...185 °F         |
| Environmental characteristic          | Standard environment |

## Ordering and shipping details

|                       |                            |
|-----------------------|----------------------------|
| Category              | 21493 - 9007 ARMS FOR AW,C |
| Discount Schedule     | DS1                        |
| GTIN                  | 00785901752820             |
| Nbr. of units in pkg. | 1                          |
| Package weight(Lbs)   | 0.16                       |
| Returnability         | Y                          |
| Country of origin     | MX                         |

## Offer Sustainability

|                                  |                                                                                                                     |
|----------------------------------|---------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status         | Green Premium product                                                                                               |
| RoHS (date code: YYWW)           | Compliant - since 1150 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity |
| REACH                            | Reference not containing SVHC above the threshold                                                                   |
| Product environmental profile    | Available                                                                                                           |
| Product end of life instructions | Need no specific recycling operations                                                                               |

|                            |                                                                                                                           |
|----------------------------|---------------------------------------------------------------------------------------------------------------------------|
| California proposition 65  | WARNING: This product can expose you to chemicals including:                                                              |
| - - - - - Substance 1      | Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and                               |
| - - - - - Substance 2      | Diisodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. |
| - - - - - More information | For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>                             |

### Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[9007HA5](#)