

ZCE07

Limit switch head, Limit switches XC Standard, ZCE, spring rod lever thermoplastic end nitrile boot





Main

Range of Product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or Component Type	Limit switch head
Device short name	ZCE
Head type	Multi-directional head
Product Compatibility	XCKP XCKT XCMD XCKD

Associated body	ZCT27N12 ZCD28 ZCP37 ZCMD29L5 ZCMD39L2 ZCT21N12 ZCP25 ZCMD37L1 ZCMD29C12 ZCT21G11 ZCMD21L1 ZCMD29L1 ZCT26N12 ZCD31 ZCMD37L2 ZCMD21C12 ZCT27P16 ZCD35 ZCMD21L5 ZCD29 ZCMD25L2 ZCMD81L1 ZCMD29L2 ZCP27 ZCT28G11 ZCMD39L1 ZCP28 ZCT27G11 ZCMD21L2 ZCP29M12 ZCMD21M12 ZCP35 ZCT21P16 ZCT25N12 ZCMD41L2 ZCMD81L2 ZCD25 ZCP31 ZCMD21L08R12 ZCP21 ZCD27 ZCD37 ZCP39 ZCMD25L5 ZCMD37L5 ZCT25G11 ZCD26 ZCP21M12 ZCMD61M12 ZCT28P16 ZCT25P16 ZCD39 ZCD21 ZCT28N12 ZCP29 ZCMD61C12 ZCMD41L5 ZCMD81L5 ZCMD25L1 ZCT26G11 ZCMD39L5 ZCD21M12 ZCT26P16 ZCMD21L08U78 ZCD29M12 ZCMD41L1 ZCP26 ZCMD69C12
Movement of operating head	Multi-directional
Type of operator	Spring rod spring return metal with nitrile boot and thermoplastic end)
Type of approach	Multi-directional approach

Complementary

Switch actuation	By any moving part
Positive opening	Without

Environment

Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	22413-LIMIT SWITCH, IEC, MINIATURE
Discount Schedule	T
GTIN	3389110191080
Nbr. of units in pkg.	1
Package weight(Lbs)	0.67 oz (19.0 g)
Returnability	Yes
Country of origin	ID

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	0.63 in (1.6 cm)
Package 1 width	0.63 in (1.6 cm)
Package 1 Length	4.96 in (12.6 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[ZCE07](#)