

ZCKE64TK

Limit switch head, Limit switches XC Standard, ZCKE, side steel roller plunger horizontal



Main

Range of Product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or Component Type	Limit switch head
Device short name	ZCKE
Head type	Plunger head
Product Compatibility	XCKJ
Associated body	ZCKJD37H7 ZCKJ1 ZCKJ2H29 ZCKJ6H7 ZCKJ6 ZCKJ2 ZCKJ21 ZCKJ8H7 ZCKJD39H29 ZCKJ8 ZCKJ7H29 ZCKJ1H7 ZCKJD31H7 ZCKJ7 ZCKJD35 ZCKJ6H29 ZCKJ2H7 ZCKJ9H29 ZCKJ11H29 ZCKJD31 ZCKJD31H29 ZCKJ9 ZCKJ1H29 ZCKJD35H29 ZCKJ5 ZCKJD37H29 ZCKJ8H29 ZCKJ5H7 ZCKJ9H7 ZCKJ5H29 ZCKJD39H7 ZCKJD35H7 ZCKJ11H7 ZCKJD37 ZCKJ7H7 ZCKJ11 ZCKJ21H29 ZCKJD39 ZCKJ21H7
Movement of operating head	Linear
Type of operator	Side roller plunger spring return metal with horizontal roller)
Type of approach	Lateral approach, 2 directions

Complementary

Switch actuation	By 30° cam
Positive opening	With
Head material	Metal

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Corrosive

Ordering and shipping details

Category	22411-LIMIT SWITCHES,IEC,XCKJ
Discount Schedule	T
GTIN	3389110914641
Nbr. of units in pkg.	1
Package weight(Lbs)	6.53 oz (185.0 g)
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.57 in (4 cm)
Package 1 width	1.85 in (4.7 cm)
Package 1 Length	3.39 in (8.6 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[ZCKE64TK](#)