

# SRT10KRMTF

APC Smart-UPS SRT Step-Down Transformer,  
10kVA, rackmount, 4U, 2x NEMA L5-20R & 2x  
NEMA L14-30R outlets



## Overview

Lead time	Usually in Stock
-----------	------------------

## Main

Main Input Voltage	208 V
Main Output Voltage	120 V 208 V 240 V
Output connector type	Hard Wire 3-wire (2PH + G) 2 Hard Wire 4-wire (2PH+N+G) 1
Provided Equipment	Mounting Hardware Rack Mounting brackets Safety guide User Manual Warranty card

## Physical

Color	Black
Height	6.85 in (17.4 cm)
Width	17.01 in (43.2 cm)
Depth	29.49 in (74.9 cm)
Net Weight	220.00 lb(US) (99.79 kg)
Mounting preference	Lower
Mounting Mode	Rack-mounted
Mounting position	Horizontal

## Input

Acceptable Input Voltage	200...240 V
Max line current	60 A
Input current limits	60 A
Load Capacity	10000 VA
Input Frequency	45...65 Hz
Number of input connectors	1 Hard Wire 3-wire (2PH + G)

## Output

Maximum Total Current Draw per Phase	60 A
Number of power socket outlets	4
Number of power socket outlets	2 NEMA L5-20R 2 NEMA L14-30R

## Conformance

Product Certifications	CE CSA UL Listed
------------------------	------------------------

## Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 % non-condensing
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 % Non-condensing
Storage altitude	0...50000 ft (0.00...15240.00 m)




## Ordering and shipping details

GTIN	731304318859
Package weight(Lbs)	275.00 lb(US) (124.74 kg)

## Packing Units

Package 1 Height	15.98 in (40.6 cm)
Package 1 width	23.62 in (60 cm)
Package 1 Length	39.37 in (100 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Take-back	Take-back program available

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SRT10KRMTF](#)