

# Product data sheet

## Characteristics

# 7F3N

9007MS/ML limit switch lever - zinc - fixed length - outside nylon roller

Product availability: Non-Stock - Not normally stocked in distribution facility



## Main

|                             |                                                           |
|-----------------------------|-----------------------------------------------------------|
| Range of product            | 9007                                                      |
| Series name                 | Miniature potted                                          |
| Product or component type   | Limit switch lever                                        |
| Device short name           | 9007MS/ML                                                 |
| Associated complete product | 9007MS04..<br>9007ML04..                                  |
| Movement of operating head  | Rotary                                                    |
| Type of operator            | Cast zinc spring return roller lever length: 1.38 in -    |
| Type of roller              | 1 nylon outside roller diameter: 0.75 in - width: 0.75 in |
| Type of approach            | Lateral approach                                          |
| Positive opening            | Without                                                   |

## Complementary

|                  |            |
|------------------|------------|
| Tracks           | 1.375 in   |
| Switch actuation | By 30° cam |
| Product weight   | 0.1 lb(US) |

## Environment

|                                       |                      |
|---------------------------------------|----------------------|
| Ambient air temperature for operation | -40...221 °F         |
| Ambient air temperature for storage   | -40...221 °F         |
| Environmental characteristic          | Standard environment |

## Ordering and shipping details

|                       |                                        |
|-----------------------|----------------------------------------|
| Category              | 22421 - LIMIT SWITCHES,ARMS FOR 9007MS |
| Discount Schedule     | DS1                                    |
| GTIN                  | 00785901118718                         |
| Nbr. of units in pkg. | 1                                      |
| Package weight(Lbs)   | 0.10000000000000001                    |
| Returnability         | N                                      |
| Country of origin     | MX                                     |

## Offer Sustainability

|                                  |                                                                                                                           |
|----------------------------------|---------------------------------------------------------------------------------------------------------------------------|
| RoHS (date code: YYWW)           | Will not be compliant                                                                                                     |
| REACH                            | Reference not containing SVHC above the threshold                                                                         |
| Product environmental profile    | Available                                                                                                                 |
| Product end of life instructions | Need no specific recycling operations                                                                                     |
| California proposition 65        | WARNING: This product can expose you to chemicals including:                                                              |
| - - - - - Substance 1            | Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and                               |
| - - - - - Substance 2            | Diisodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. |
| - - - - - More information       | For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>                             |

Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[7F3N](#)