

Product availability: Non-Stock - Not normally stocked in distribution facility



## Main

|                                    |                   |
|------------------------------------|-------------------|
| Accessory / separate part category | Cabling accessory |
| Accessory / separate part type     | Jumper cable      |

## Complementary

|                             |                                                  |
|-----------------------------|--------------------------------------------------|
| Jumper cable end 1          | M12 male, :4 pins (straight), fixing: screw-on   |
| Jumper cable end 2          | M12 female, :4 pins (straight), fixing: screw-on |
| Cable composition           | 4 x 0.34 mm <sup>2</sup>                         |
| Cable length                | 16.4 ft (5 m)                                    |
| Wire insulation material    | PUR                                              |
| Cable outer diameter        | 0.2 in (5.2 mm)                                  |
| System Voltage              | 250 V AC<br>300 V DC                             |
| Line Rated Current          | 4 A                                              |
| Insulation resistance       | >= 1000 MOhm                                     |
| Resistance across terminals | <= 5000 mOhm                                     |
| Product weight              | 0.21 lb(US) (0.095 kg)                           |

## Environment

|                                       |                                                                           |
|---------------------------------------|---------------------------------------------------------------------------|
| IP degree of protection               | IP65<br>IP69K<br>IP67                                                     |
| Product certifications                | cULus                                                                     |
| Ambient air temperature for operation | -31...194 °F (-35...90 °C) (static)<br>23...194 °F (-5...90 °C) (flexing) |
| Ambient air temperature for storage   | -31...212 °F (-35...100 °C)                                               |

## Ordering and shipping details

|                       |                        |
|-----------------------|------------------------|
| Category              | 22483 - MACHINE CABLES |
| Discount Schedule     | DS3                    |
| GTIN                  | 003389119023849        |
| Nbr. of units in pkg. | 1                      |
| Package weight(Lbs)   | 0.23000000000000001    |
| Returnability         | N                      |
| Country of origin     | CZ                     |


## Offer Sustainability

|                                  |                                                                                                                                                                                                        |
|----------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status         | Green Premium product                                                                                                                                                                                  |
| RoHS (date code: YYWW)           | Compliant - since 0802 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity |
| REACH                            | Reference not containing SVHC above the threshold                                                                                                                                                      |
| Product environmental profile    | Available                                                                                                                                                                                              |
| Product end of life instructions | Available                                                                                                                                                                                              |
| California proposition 65        | WARNING: This product can expose you to chemicals including:                                                                                                                                           |
| - - - - - Substance 1            | Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and                                                                                                            |
| - - - - - Substance 2            | Diisodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.                                                                              |
| - - - - - More information       | For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>                                                                                                          |

## Contractual warranty


|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

## Dimensions



L : Length of cable

## Connections and Schemes



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XZCR1511041C5](#)