

Product availability: Non-Stock - Not normally stocked in distribution facility



### Main

|                                 |                         |
|---------------------------------|-------------------------|
| Range of product                | Harmony 9001K           |
| Product or component type       | Illuminated push-button |
| Device short name               | K                       |
| Type of operator                | Spring return           |
| Operator profile                | Red flush               |
| Operator additional information | Full guard in plastic   |

### Complementary

|                                |                              |
|--------------------------------|------------------------------|
| Bezel material                 | Chromium plated metal        |
| Mounting diameter              | 1.18 in (30 mm)              |
| Light source                   | Incandescent                 |
| Bulb base                      | BA 9s                        |
| Light block supply             | Via integral transformer     |
| [Us] rated supply voltage      | 110...120 V AC               |
| Contacts type and composition  | 1 NO                         |
| Connections - terminals        | Screw clamp terminals        |
| Operating position             | Any position                 |
| [Ie] rated operational current | 10 A (AC-15)<br>10 A (DC-13) |
| Contact operation              | Standard                     |
| Device presentation            | Complete product             |

### Environment

|                           |                                                                            |
|---------------------------|----------------------------------------------------------------------------|
| Product certifications    | CE<br>UL listed file E42259 CCN NKCR<br>CSA LR 25490 class 3211 03<br>NEMA |
| NEMA degree of protection | NEMA 1/2/3/3R/4/6/12/13                                                    |

### Ordering and shipping details

|                       |                               |
|-----------------------|-------------------------------|
| Category              | 21426 - 9001 K (NOT KA,KM,KX) |
| Discount Schedule     | CS1                           |
| GTIN                  | 00785901027034                |
| Nbr. of units in pkg. | 1                             |
| Package weight(Lbs)   | 0.5                           |
| Returnability         | N                             |
| Country of origin     | MX                            |

### Offer Sustainability

|                           |                                                                                                                                  |
|---------------------------|----------------------------------------------------------------------------------------------------------------------------------|
| California proposition 65 | WARNING: This product can expose you to chemicals including:                                                                     |
| ----- Substance 1         | Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. |
| ----- More information    | For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>                                    |

Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[9001K1L1RH5](#)