

Product availability: Stock - Normally stocked in distribution facility



Main

Range of product	ConneXium
Product or component type	Ethernet TCP/IP unmanaged switch
Concept	Transparent Ready
Communication port protocol	Ethernet TCP/IP
Port Ethernet	10BASE-T/100BASE-TX - 5 port(s) copper cable
Maximum number of switches in cascade	Unlimited

Complementary

Integrated connection type	Shielded RJ45 copper cable
Transmission support medium	Twisted shielded pairs cable CAT 5E copper cable
Ethernet service	Storage and re-routing of received data Automatic change of polarity Auto MDI/MDX Automatic negotiation of 10/100 Mbit/s and duplex mode
[Us] rated supply voltage	24 V
Supply voltage limits	9.6...32 V DC SELV
Power consumption in W	2.2 W
Electrical connection	Removable connector 3 ways power supply
Marking	CE
Local signalling	1 LED power supply 1 LED per channel copper port activity 1 LED per channel 10 or 100 Mbit/s data rate
Ethernet cabling system	TF switches
Width	0.98 in (25 mm)
Height	4.49 in (114 mm)
Depth	3.11 in (79 mm)
Product weight	0.25 lb(US) (0.113 kg)

Environment

Ambient air temperature for operation	32...140 °F (0...60 °C)
Relative humidity	> 0...95 % without condensation
IP degree of protection	IP30
Standards	CUL 508 CSA C22.2 No 142
Product certifications	CE

Ordering and shipping details

Category	18225 - PLC NTRK HRDWR & PROWORX SOFTWARE
Discount Schedule	PC41
GTIN	00785901596288
Nbr. of units in pkg.	1
Package weight(Lbs)	0.38

Returnability	Y
Country of origin	DE


Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0744 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Power Wiring



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[TCSESU053FN0](#)