



Main

Range of Product	Harmony XAC
Product or Component Type	Selector switch
Component name	ZA2
Product Compatibility	XACA

Complementary

Marking	Unmarked
Cap/operator or lens colour	Black
Mounting Location	Front of enclosure
Sale per indivisible quantity	1
Net Weight	0.09 lb(US) (0.042 kg)

Environment

Standards	CSA C22.2 No 14 UL 508 EN/IEC 60204-32 EN/IEC 60947-5-1
Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Vibration resistance	15 gn 10...500 Hz)IEC 60068-2-6
Shock resistance	100 gn IEC 60068-2-27
Overvoltage category	Class II IEC 61140
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK08 EN 50102

Ordering and shipping details

Category	22460 - PUSHBUTTONS 22MM (PLASTIC)
Discount Schedule	CS2
GTIN	3389110648645
Nbr. of units in pkg.	1
Package weight(Lbs)	1.80 oz (50.9 g)
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.18 in (3 cm)
Package 1 width	1.38 in (3.5 cm)
Package 1 Length	2.36 in (6 cm)
Unit Type of Package 2	BB1

Number of Units in Package 2	10
Package 2 Weight	17.99 oz (510 g)
Package 2 Height	1.18 in (3 cm)
Package 2 width	5.12 in (13 cm)
Package 2 Length	5.91 in (15 cm)
Unit Type of Package 3	S02
Number of Units in Package 3	50
Package 3 Weight	6.38 lb(US) (2.894 kg)
Package 3 Height	5.91 in (15 cm)
Package 3 width	11.81 in (30 cm)
Package 3 Length	15.75 in (40 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[ZA2BG6](#)