

ZBE1013

single contact block for head Ø22 1NO silver alloy Faston connector

Product availability: Stock - Normally stocked in distribution facility



Main

Range of product	Harmony XB5 Harmony XB4
Product or component type	Contact block
Device short name	ZBE
Sale per indivisible quantity	5
IP degree of protection	IP20 IEC 60529
Contacts type and composition	1 NO
Contact operation	Slow-break
Contact block type	Single
Contacts usage	Standard contacts
Connections - terminals	Faston connector 1 x 6.35 mm Faston connector 2 x 2.8 mm

Complementary

Product weight	0.02 lb(US) (0.011 kg)
Positive opening	Without
Operating travel	0.1 in (2.6 mm) NO changing electrical state 0.17 in (4.3 mm) total travel
Operating force	2.3 N NO changing electrical state
Mechanical durability	10000000 cycles
Contacts material	Silver alloy (Ag/Ni)
[Ui] rated insulation voltage	250 V 3 EN 60947-1
Electrical reliability	$\Lambda < 10\exp(-7)$ 1 mA in clean environment EN/IEC 60947-5-4 $\Lambda < 10\exp(-8)$ 5 mA in clean environment EN/IEC 60947-5-4
Mounting of block	Front mounting
Condition of use	Mounting on push-button collar
Electrical composition code	C1 <= 9 C2 <= 7 C3 <= 6 C4 <= 4 C5 <= 5 C6 <= 3 C7 <= 4 C8 <= 2 C9 <= 3 C12 <= 6 M1 <= 6 M2 <= 4 M3 <= 4 M5 <= 2 M6 <= 2 M7 <= 6 M8 <= 4 M9 <= 2 SF1 <= 3 SF2 <= 2 MF1 <= 2 MF2 <= 2 C10 <= 2 M4 <= 2 C13 <= 1
Compatibility code	ZBE

Environment

Protective treatment	TH
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Ambient air temperature for operation	-40...158 °F (-40...70 °C)
Standards	EN/IEC 60947-5-1 CSA C22.2 No 14 EN/IEC 60947-1 JIS C 4520 EN/IEC 60947-5-4 UL 508
Product certifications	LROS (Lloyds register of shipping) BV RINA CSA DNV UL GL
Vibration resistance	5 gn 2...500 Hz IEC 60068-2-6
Shock resistance	30 gn 18 ms half sine wave acceleration IEC 60068-2-27 50 gn 11 ms half sine wave acceleration IEC 60068-2-27

Ordering and shipping details

Category	22469 - PUSHBUTTON,22MM ACCESSORIES-NEW
Discount Schedule	CS2
GTIN	00785901420842
Nbr. of units in pkg.	5
Package weight(Lbs)	2.999999999999999E-2
Returnability	Y
Country of origin	FR

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Nickel compounds, which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[ZBE1013](#)