

## Product data sheet

### Characteristics

# 9001SKS43BH13

30mm Push Button, Type SK, selector switch, 3 position, C cam, black knob, 1NO and 1NC

Product availability: Stock - Normally stocked in distribution facility



### Main

|                           |                     |
|---------------------------|---------------------|
| Range of product          | Harmony 9001SK      |
| Product or component type | Selector switch     |
| Device short name         | 9001SK              |
| Type of operator          | Stay put            |
| Operator profile          | Black standard knob |

### Complementary

|                               |                                  |
|-------------------------------|----------------------------------|
| Bezel material                | Plastic                          |
| Mounting diameter             | 1.18 in (30 mm)                  |
| Operator position information | 3 positions                      |
| Contacts type and composition | 1 C/O                            |
| Product compatibility         | 9001KA1, mounting on side 1 or 2 |
| Device presentation           | Complete product                 |

### Environment

|                                       |                                                                   |
|---------------------------------------|-------------------------------------------------------------------|
| Protective treatment                  | TC                                                                |
| Ambient air temperature for storage   | -40...158 °F (-40...70 °C)                                        |
| Ambient air temperature for operation | -13...158 °F (-25...70 °C)                                        |
| Electrical shock protection class     | Class II conforming to IEC 61140                                  |
| IP degree of protection               | IP66 conforming to IEC 60529                                      |
| NEMA degree of protection             | NEMA 1/2/3/3R/4/4X/6/12/13                                        |
| Product certifications                | UL listed file E42259 CCN NKCR<br>CE<br>CSA LR24590 class 3211 03 |

### Ordering and shipping details

|                       |                     |
|-----------------------|---------------------|
| Category              | 21429 - 9001 SK,SKY |
| Discount Schedule     | CS1                 |
| GTIN                  | 00785901043720      |
| Nbr. of units in pkg. | 1                   |
| Package weight(Lbs)   | 0.19                |
| Returnability         | Y                   |
| Country of origin     | MX                  |

## Offer Sustainability

|                            |                                                                                                                                                                                                        |
|----------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| RoHS (date code: YYWW)     | Compliant - since 0921 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity |
| REACH                      | Reference not containing SVHC above the threshold                                                                                                                                                      |
| California proposition 65  | WARNING: This product can expose you to chemicals including:                                                                                                                                           |
| - - - - - Substance 1      | Nickel compounds, which is known to the State of California to cause cancer, and                                                                                                                       |
| - - - - - Substance 2      | Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.                                                                             |
| - - - - - More information | For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>                                                                                                          |

## Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[9001SKS43BH13](#)