



Main

Range	Linergy
Product name	FT
Device short name	GV1G
Product or Component Type	Terminal block
Accessory / separate part category	Connection accessory
Poles description	3P
Range compatibility	TeSys GV2 TeSys D TeSys K TeSys U TeSys LS1

Complementary

[Ie] rated operational current	63 A
Mounting Location	Top
IP degree of protection	IP20 conforming to IEC 60529
[Ui] rated insulation voltage	690 V IEC 60947-1
Connections - terminals	Screw clamp terminals 1 solid AWG 4 Screw clamp terminals 1 0.00...0.02 in ² (1.5...16 mm ²) flexible with cable end Screw clamp terminals 1 0.00...0.02 in ² (1.5...16 mm ²) flexible without cable end Screw clamp terminals 1 0.00...0.04 in ² (1.5...25 mm ²) solid Screw clamp terminals 2 0.00...0.01 in ² (1.5...4 mm ²) flexible with cable end Screw clamp terminals 2 0.00...0.01 in ² (1.5...6 mm ²) solid Screw clamp terminals 2 0.00...0.01 in ² (2.5...4 mm ²) flexible without cable end Screw clamp terminals 1 flexible AWG 4
Tightening torque	15.05 Lbf.in (1.7 N.m) screw clamp terminals 19.47 lbf.in (2.2 N.m) connector
Net Weight	0.09 lb(US) (0.04 kg)

Ordering and shipping details

Category	22366 - MAN STR PROTECTORS-GV1/GV3
Discount Schedule	I11
GTIN	3389110212570
Nbr. of units in pkg.	1
Package weight(Lbs)	1.69 oz (48 g)
Returnability	Yes
Country of origin	RO

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.57 in (4 cm)
Package 1 width	1.97 in (5 cm)
Package 1 Length	2.17 in (5.5 cm)
Unit Type of Package 2	S02
Number of Units in Package 2	70
Package 2 Weight	8.11 lb(US) (3.678 kg)
Package 2 Height	5.91 in (15 cm)
Package 2 width	11.81 in (30 cm)

Package 2 Length	15.75 in (40 cm)
Unit Type of Package 3	P06
Number of Units in Package 3	1120
Package 3 Weight	150.31 lb(US) (68.18 kg)
Package 3 Height	30.31 in (77 cm)
Package 3 width	31.50 in (80 cm)
Package 3 Length	23.62 in (60 cm)


Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Sets of Busbars GV2G... with Terminal Block GV1G09



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[GV1G09](#)