



Main

Range of Product	Harmony XK
Product or Component Type	Complete joystick controller
Product Specific Application	Light hoisting applications

Complementary

Device short name	XKB
Bezel material	Metal
Fixing collar material	Metal
Sale per indivisible quantity	1
Protective treatment	TC
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Ambient air temperature for operation	-4...158 °F (-20...70 °C)
Overvoltage category	Class I IEC 61140
IP degree of protection	IP54 IEC 60529 IP20 IEC 60529
Standards	UL 508 EN/IEC 60947-5-1 CSA C22.2 No 14
Product Certifications	RRS UL CSA CCC
Contact code designation	Q300 A300
Operator position information	All positions
Operator profile	Handle with zero position mechanical interlock
Notch per direction	1...3 12°-20°-28° for each direction
Mechanical durability	1000000 cycles
Vibration resistance	6 gn 1...70 Hz)IEC 60068-2-6
Shock resistance	20 gn 11 ms) IEC 60068-2-27
Connections - terminals	Captive screw clamp terminals, <= 2 x 1.5 mm ² with cable end Captive screw clamp terminals, <= 1 x 2.5 mm ² without cable end Captive screw clamp terminals, >= 1 x 0.5 mm ²
Short-circuit protection	10 A cartridge fuse gG EN/IEC 60947-5-1
[Ith] conventional free air thermal current	10 A EN/IEC 60947-5-1 10 A CSA C22.2 No 14 10 A UL 508
[Ui] rated insulation voltage	500 V 3)IEC 60947-1

Ordering and shipping details

Category	22474 - PUSHBUTTON,CRANE JOYSTICKS
Discount Schedule	I
GTIN	785901543671
Nbr. of units in pkg.	1
Package weight(Lbs)	32.00 oz (907.185 g)
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	9.50 in (24.13 cm)
Package 1 width	6.50 in (16.51 cm)
Package 1 Length	6.40 in (16.256 cm)

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XKBA14200](#)