



Main

Range of Product	Harmony XK
Product or Component Type	Complete joystick controller
Product Specific Application	Medium hoisting applications
Device short name	XKD
Sale per indivisible quantity	1

Complementary

Bezel material	Metal
Fixing collar material	Metal
Protective treatment	TC
Operator position information	All positions
Operator profile	Dead man's handle, 1 NC + 1 NO, slow-break
Positive opening	Slow break, double-break with
Connections - terminals	Captive screw clamp terminals, $\leq 2 \times 1.5 \text{ mm}^2$ with cable end Captive screw clamp terminals, $\leq 1 \times 2.5 \text{ mm}^2$ without cable end Captive screw clamp terminals, $\geq 1 \times 0.5 \text{ mm}^2$
Short-circuit protection	10 A cartridge fuse gG EN/IEC 60947-5-1
[Ith] conventional free air thermal current	10 A EN/IEC 60947-5-1 10 A CSA C22.2 No 14
[Ui] rated insulation voltage	500 V 3) IEC 60947-1

Environment

Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Ambient air temperature for operation	-4...158 °F (-20...70 °C)
Overvoltage category	Class I IEC 61140
Standards	EN/IEC 60947-5-1 CSA C22.2 No 14
Mechanical durability	3000000 cycles
Vibration resistance	2 gn 10...500 Hz) IEC 60068-2-6
Shock resistance	15 gn 11 ms) IEC 60068-2-27

Ordering and shipping details

Category	22474 - PUSHBUTTON, CRANE JOYSTICKS
Discount Schedule	I
GTIN	3606485374925
Nbr. of units in pkg.	1
Package weight(Lbs)	4.94 lb(US) (2.24 kg)
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	9.45 in (24 cm)
Package 1 width	5.91 in (15 cm)
Package 1 Length	5.91 in (15 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XKDF1435666](#)