

Product availability: Non-Stock - Not normally stocked in distribution facility



### Main

Range of product	Harmony XVR
Product or component type	Prewired rotating mirror beacon
Sound signalling	Without
Device short name	XVR
Mounting diameter	5.12 in (130 mm)
IP degree of protection	IP66 conforming to IEC 60529 IP67 conforming to IEC 60529
[Us] rated supply voltage	24 V AC/DC
Light source	High luminosity LED, orange

### Complementary

Material	ABS (acrylonitrile butadiene-styrene) (body part) PC (globe)
CAD overall width	5.12 in (130 mm)
CAD overall depth	5.12 in (130 mm)
Product weight	1.81 lb(US) (0.82 kg)
Marking	CE
Product mounting	By 3 M6 screws
[Uimp] rated impulse withstand voltage	0.8 kV
Current consumption	125 mA
Flashing frequency	2.7 Hz
Clamping connection capacity	1.25 mm <sup>2</sup>
AWG gauge	AWG 18
Cable length	15.75 in (400 mm)


### Environment

Standards	EN/IEC 61000-6-4 EN/IEC 61000-6-2
Protective treatment	TC
Ambient air temperature for storage	-31...158 °F (-35...70 °C)
Ambient air temperature for operation	-22...122 °F (-30...50 °C)
Electrical shock protection class	Class II conforming to IEC 61140

### Ordering and shipping details

Category	22617 - XVC TOWER LIGHTS
Discount Schedule	XV
GTIN	00785901944812
Nbr. of units in pkg.	1
Package weight(Lbs)	2.4900000000000002
Returnability	N
Country of origin	ID

## Offer Sustainability


Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1611 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------

## Rotating Mirror Beacon

### Dimensions




---

Rotating Mirror Beacon

---

Panel Cut-out



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XVR13B05L](#)