

### Main

|                           |                               |
|---------------------------|-------------------------------|
| Range of Product          | Hyde Park                     |
| Sensor Type               | Ultrasonic sensor             |
| Series name               | Standard format               |
| Device short name         | SM952                         |
| Sensor design             | Ø 30 mm                       |
| Material                  | Stainless steel               |
| [Us] rated supply voltage | 12...24 V DC                  |
| Electrical connection     | 1 connector micro             |
| [Sd] sensing range        | 0.67...26.25 ft (0.203...8 m) |
| IP degree of protection   | IP66                          |

### Complementary

|                        |         |
|------------------------|---------|
| Type of sensing window | Fixed   |
| Enclosure Material     | Plastic |
| Transmission frequency | 75 kHz  |
| Maximum delay response | 250 ms  |

### Ordering and shipping details

|                       |                                    |
|-----------------------|------------------------------------|
| Category              | 22490 - SENSORS-ULTRASONIC (XX5,6) |
| Discount Schedule     | DS2                                |
| GTIN                  | 3389119120791                      |
| Nbr. of units in pkg. | 1                                  |
| Package weight(Lbs)   | 3.20 oz (90.719 g)                 |
| Returnability         | No                                 |
| Country of origin     | US                                 |

### Packing Units

|                        |                     |
|------------------------|---------------------|
| Unit Type of Package 1 | PCE                 |
| Package 1 Height       | 1.80 in (4.572 cm)  |
| Package 1 width        | 3.90 in (9.906 cm)  |
| Package 1 Length       | 5.30 in (13.462 cm) |

### Offer Sustainability

|                           |                                                                                                                                                                                                                                                                                                                                                                                   |
|---------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| California proposition 65 | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| RECh Regulation           |  <a href="#">RECh Declaration</a>                                                                                                                                                                                                                                                              |
| EU RoHS Directive         | Not applicable, out of EU RoHS legal scope                                                                                                                                                                                                                                                                                                                                        |

### Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SM952A836000](#)