



Product availability: Stock - Normally stocked in distribution facility



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCKD
Head type	Plunger head
Product compatibility	XCKL XCKM XCKS

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Associated body	ZCKL5 ZCKMD31 ZCKM7H7 ZCKM5 ZCKS8 ZCKS2 ZCKLD39H7 ZCKSD35 ZCKM6H29 ZCKM1H29 ZCKM8H7 ZCKS5 ZCKMD31H29 ZCKLD35 ZCKL8 ZCKS5H29 ZCKM9 ZCKLD37H7 ZCKS2H29 ZCKS8H29 ZCKSD37H29 ZCKM1H7 ZCKL1 ZCKM6 ZCKS6 ZCKMD31H7 ZCKMD37H29 ZCKSD37 ZCKL7 ZCKM7 ZCKLD39 ZCKMD37H7 ZCKS7 ZCKL6H7 ZCKL6 ZCKS7H29 ZCKM5H7 ZCKM6H7 ZCKSD31H29 ZCKL7H7 ZCKL1H7 ZCKMD39H29 ZCKL8H7 ZCKS1 ZCKMD35H29 ZCKLD37 ZCKSD39H29 ZCKM5H29 ZCKS1H29 ZCKLD31H7 ZCKMD35H7 ZCKMD37 ZCKSD31 ZCKM1 ZCKMD39H7 ZCKS9H29 ZCKM7H29 ZCKS6H29 ZCKSD35H29 ZCKSD39 ZCKM8 ZCKS9 ZCKM8H29 ZCKMD35 ZCKLD31 ZCKMD39 ZCKLD35H7 ZCKL5H7 ZCKM9H29
Movement of operating head	Linear
Type of operator	Roller plunger spring return metal
Type of approach	Lateral approach 2 directions

Complementary

Switch actuation	By 30° cam
Positive opening	With
Head material	Plastic

Environment

Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	22416 - LIMIT SWITCHES,IEC,XCKL
Discount Schedule	T
GTIN	00785901646716
Nbr. of units in pkg.	1
Package weight(Lbs)	0.10000000000000001
Returnability	Y
Country of origin	ID

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0922 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
- - - - - Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[ZCKD02](#)