

P610

APC Essential SurgeArrest 6 Outlet 10 Foot Cord, 120V



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	120 V
Plug standard	NEMA 5-15P
Cable length	10 ft (3.05 m)
Number of cables	1
Provided equipment	User Manual

Physical

Color	Beige
Height	11.26 in (28.6 cm)
Width	2.01 in (5.1 cm)
Depth	1.50 in (3.8 cm)
Net Weight	1.30 lb(US) (0.59 kg)
Mounting preference	No preference
Mounting Mode	Rack-mounted

Input

Input power	1200 W
Maximum Line Current per phase	15 A
Input Frequency	50/60 Hz +/- 5 Hz auto-sensing
Maximum Input Current per Phase	15 A
Switching current capacity	15 A

Output

Number of power socket outlets	6
Outlet standard	NEMA 5-15R

Conformance

UL 1449 TVSS Rating	400
Product certifications	ETL
Equipment protection policy	Lifetime : \$50000

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Surge Protection and Filtering

NM Surge Response Time (ns)	1 ns common mode
Common mode rejection	40 dB
Peak current	72 kA common mode 60 kA per phase normal mode
Surge energy rating	1080 J

Ordering and shipping details

Category	11309 - APC RESALE PRODUCTS
GTIN	00731304282709
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No

Packing Units

Package 1 Height	12.01 in (30.5 cm)
Package 1 width	5.51 in (14 cm)
Package 1 Length	1.81 in (4.6 cm)
SCC14	10731304282706
Number of Units in Package 2	6
Package 2 Weight	10.45 lb(US) (4.74 kg)
Package 2 Height	5.9 in (149.86 mm)
Package 2 width	12.25 in (311.15 mm)
Package 2 Length	11.63 in (295.40 mm)
Number of Units in Package 3	864

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	Limited Lifetime
----------	------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[P610](#)