

Product availability: Stock - Normally stocked in distribution facility



### Main

Range	TeSys
Product name	TeSys LK
Product or component type	Disconnect Switch
Disconnecter device type	Non-fusible disconnect switch
Suitability for isolation	Yes

### Complementary

Poles description	3P
Network type	AC
Network frequency	50/60 Hz
[Ie] rated operational current	30 A conforming to CSA 30 A conforming to UL 32 A (AC-22A) at 400 V AC conforming to IEC 32 A (AC-23A) at 400 V AC conforming to IEC 32 A (AC-22A) at 690 V AC conforming to IEC 32 A (AC-23A) at 690 V AC conforming to IEC
System Voltage	600 V AC 50/60 Hz
[Ui] rated insulation voltage	690 V
Control type	Rotary handle
Type of operating handle	External right side External frontal
Mounting support	Plate
[Uimp] rated impulse withstand voltage	8 kV conforming to IEC
Rated power in W	15 kW at 400 V 18.5 kW at 500 V 25 kW at 690 V
Rated power in hp	10 hp at 240 V 30 A AC 20 hp at 480 V 28 A AC 25 hp at 600 V 28 A AC
[Icw] rated short-time withstand current	5.5 kA
Mechanical durability	10000 cycles
Electrical durability	6000 cycles
Connections - terminals	Lugs-ring terminals 1 cable(s) 0.01 in <sup>2</sup> (4 mm <sup>2</sup> )
Height	4.92 in (125 mm)
Width	3.13 in (79.5 mm)
Depth	2.52 in (64 mm)

### Environment

Standards	CSA C22.2 No 4 IEC 60947-3 UL98
Product certifications	CSA UL CE

## Ordering and shipping details

Category	22640 - IEC DISCONNECT-GS1,LK3
Discount Schedule	I11
GTIN	00785901333463
Nbr. of units in pkg.	1
Package weight(Lbs)	1.3700000000000001
Returnability	Y
Country of origin	CN

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0844 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Available
California proposition 65	WARNING: Cancer - www.P65Warnings.ca.gov

## Contractual warranty

Warranty period	18 months
-----------------	-----------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[LK4DU3CN](#)