

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range	TeSys
Product or component type	Contactor coil
Range compatibility	TeSys LC1B contactor TeSys CR1B.32 contactor TeSys CR1B.34 contactor TeSys CR1B.33 contactor
Control circuit type	AC DC
Coil type	Low consumption
[Uc] control circuit voltage	109...136 V DC 126...155 V AC 50...400 Hz 137...173 V DC 157...196 V AC 50...400 Hz 160...201 V DC 181...226 V DC 182...228 V AC 50...400 Hz 205...259 V AC 50...400 Hz 220 V DC 220...230 V AC 50...400 Hz 240 V AC 50...400 Hz

Complementary

Average resistance	32.5 Ohm at 68 °F (20 °C)
Inrush power in VA	1100...1300 VA 3P 1300...1600 VA 4P 450...620 VA 1P 720...1000 VA 2P
Inrush power in W	1100...1400 W for 4P 380...520 W for 1P 600...800 W for 2P 900...1100 W for 3P
Hold-in power consumption in VA	0.15...0.2 VA 50...400 Hz 1P 0.35...0.5 VA 50...400 Hz 2P 0.7...1 VA 50...400 Hz 3P 1.2...1.6 VA 50...400 Hz 4P
Hold-in power consumption in W	0.15...0.2 W for 1P 0.35...0.5 W for 2P 0.7...1 W for 3P 1.2...1.6 W for 4P
Mechanical durability	1200000 cycles
Product weight	2.47 lb(US) (1.12 kg)

Environment

Heat dissipation	15...20 W at 50...400 Hz 2P 24...30 W at 50...400 Hz 3P 35...45 W at 50...400 Hz 4P 7...10 W at 50...400 Hz 1P
------------------	---

Ordering and shipping details

Category	18074 - SPARE PARTS DISCOUNT I11
Discount Schedule	I11
GTIN	00785901289326
Nbr. of units in pkg.	1
Package weight(Lbs)	2.7000000000000002

Returnability	N
Country of origin	FR

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0801 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[WB1KB124](#)