




Main

Product or Component Type	Controllers separate parts
Accessory / separate part category	Control accessory
Product Specific Application	Light hoisting applications
Product Compatibility	XKB
Accessory / Separate Part Type	Contacts block
Accessory / separate part specific characteristic	For use with zero (center) position interlocking handle For use with simple handle

Complementary

Contact block per direction [control circuit]	4 per movement 1 zero (center) position 2 zero per movement
Electrical connection	Screw clamp terminal 1 x 0.5...1 x 1.5 mm ² Screw clamp terminal 1 x 0.5...1 x 2.5 mm ²
Enclosure/cubicle description	Monobloc
Contacts type and composition	8 NO 1 NC 2 NC
Contact operation	Double-break Slow-break
[Ith] conventional free air thermal current	10 A IEC 337-1 10 A NF C 63-140 10 A VDE 0660 10 A CSA C22.2 No 14
[Ui] rated insulation voltage	500 V AC/DC IEC 158-1 500 V AC/DC NF C 20-040 500 V AC/DC VDE 0110
Maximum resistance across terminals	25 mOhm 1 A NF C 93-050
Positive opening	With
Short-circuit protection	10 A cartridge fuse gG IEC 337-1B 10 A cartridge fuse gG VDE 0660 part 2
Electrical durability	1000000 Cycles DC inductive 120 V 75 IEC 337-1 DC-11 60 cyc/mn 0.5 1000000 Cycles DC inductive 24 V 90 IEC 337-1 DC-11 60 cyc/mn 0.5 1000000 cycles DC inductive 48 V 90 IEC 337-1 DC-11 60 cyc/mn 0.5
Net Weight	0.47 lb(US) (0.215 kg)

Environment

Standards	CENELEC EN 50013
-----------	------------------

Ordering and shipping details

Category	22474 - PUSHBUTTON,CRANE JOYSTICKS
Discount Schedule	I
GTIN	3389110929522
Nbr. of units in pkg.	1
Package weight(Lbs)	7.19 oz (203.9 g)
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.38 in (3.5 cm)
Package 1 width	4.02 in (10.2 cm)
Package 1 Length	4.06 in (10.3 cm)
Unit Type of Package 2	S01
Number of Units in Package 2	10
Package 2 Weight	4.94 lb(US) (2.241 kg)
Package 2 Height	5.91 in (15 cm)
Package 2 width	5.91 in (15 cm)
Package 2 Length	15.75 in (40 cm)
Package 3 Height	5.91 in (15 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XKBZ992](#)