



Main

Product or Component Type	Controllers separate parts
Accessory / separate part category	Control accessory
Product Specific Application	Heavy hoisting applications
Product Compatibility	XKM
Accessory / Separate Part Type	Contact block
Number of contacts	4
Contact blow-out type	Magnetic

Complementary

Electrical connection	Screw clamp terminal 1 x 1.5...2 x 2.5 mm²
Contact operation	Double-break Slow-break
[Ith] conventional free air thermal current	20 A IEC 337-1 20 A NF C 63-140 20 A VDE 0660
[Ui] rated insulation voltage	500 V AC/DC IEC 158-1 500 V AC/DC NF C 20-040 500 V AC/DC VDE 0110 600 V CSA C22.2 No 14
Positive opening	With
Maximum resistance across terminals	25 MOhm 1 A NF C 93-050
Short-circuit protection	20 A cartridge fuse gG IEC 337-1B 20 A cartridge fuse gG VDE 0660 part 2
Electrical durability	3000000 Cycles DC inductive 120 V 100 IEC 337-1 DC-11 60 cyc/mn 0.5 3000000 Cycles DC inductive 24 V 90 IEC 337-1 DC-11 60 cyc/mn 0.5 3000000 cycles DC inductive 48 V 100 IEC 337-1 DC-11 60 cyc/mn 0.5
Net Weight	0.74 lb(US) (0.335 kg)

Environment

Standards	CENELEC EN 50013
-----------	------------------

Ordering and shipping details

Category	22474 - PUSHBUTTON,CRANE JOYSTICKS
Discount Schedule	I
GTIN	3389110929935
Nbr. of units in pkg.	1
Package weight(Lbs)	12.20 oz (346 g)
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.09 in (5.3 cm)
Package 1 width	3.54 in (9 cm)
Package 1 Length	5.91 in (15 cm)
Unit Type of Package 2	S02
Number of Units in Package 2	13
Package 2 Weight	11.44 lb(US) (5.187 kg)
Package 2 Height	5.91 in (15 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XKMA992](#)