



## Main

Product or Component Type	Controllers separate parts
Accessory / separate part category	Control accessory
Product Specific Application	Light hoisting applications
Product Compatibility	XKB
Accessory / Separate Part Type	Contacts block
Accessory / separate part specific characteristic	For use with built-in push-button handle For use with Dead man's handle

## Complementary

Contact block per direction [control circuit]	1 zero (center) position 2 zero per movement 4 per movement
Electrical connection	Screw clamp terminal 1 x 0.5...1 x 1.5 mm <sup>2</sup> Screw clamp terminal 1 x 0.5...1 x 2.5 mm <sup>2</sup>
Enclosure/cubicle description	Monobloc
Contacts type and composition	1 NO 2 NC 8 NO
Contact operation	Double-break Slow-break
[I <sub>th</sub> ] conventional free air thermal current	10 A IEC 337-1 10 A NF C 63-140 10 A VDE 0660 10 A CSA C22.2 No 14
[U <sub>i</sub> ] rated insulation voltage	500 V AC/DC IEC 158-1 500 V AC/DC NF C 20-040 500 V AC/DC VDE 0110
Maximum resistance across terminals	25 mOhm 1 A NF C 93-050
Positive opening	With
Short-circuit protection	10 A cartridge fuse gG IEC 337-1B 10 A cartridge fuse gG VDE 0660 part 2
Electrical durability	1000000 Cycles DC inductive 120 V 75 IEC 337-1 DC-11 60 cyc/mn 0.5 1000000 Cycles DC inductive 24 V 90 IEC 337-1 DC-11 60 cyc/mn 0.5 1000000 cycles DC inductive 48 V 90 IEC 337-1 DC-11 60 cyc/mn 0.5
Net Weight	0.47 lb(US) (0.215 kg)

## Environment

Standards	CENELEC EN 50013
-----------	------------------

## Ordering and shipping details

Category	22474 - PUSHBUTTON,CRANE JOYSTICKS
Discount Schedule	I
GTIN	3389110929539
Nbr. of units in pkg.	1
Package weight(Lbs)	7.16 oz (203 g)
Returnability	No
Country of origin	FR

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	4.06 in (10.3 cm)
Package 1 width	1.38 in (3.5 cm)
Package 1 Length	4.06 in (10.3 cm)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

## Contractual warranty

Warranty	18 months
----------	-----------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XKBZ994](#)