




# SERPAC 191 (exploded isometric)

Electronic Enclosures

- Click on image to show toolbar. Use ▶ || to Play/Pause Animation.
- Left click and drag on image to move 3D model.



Water proofing gasket  
PS19 optional.  
see note #2



- Zoom in & out with center wheel.
- Pause at any moment to view and or print views.
- Change the views to ortho and section views if needed from the Views pull down menu.
- Explore options included in the tool bar like: Views, Transparency of model, Lighting type, etc.







| PART NO. | DESCRIPTION (Included)   | ACCESSORIES (Optional) |                |
|----------|--------------------------|------------------------|----------------|
| 9-1      | TOP                      | PART NO.               | DESCRIPTION    |
| 19       | BOTTOM                   | 50                     | Non-skid Feet  |
| 6005     | #4X3/8" Self tapping (6) | PS19                   | Perimeter Seal |
|          |                          |                        |                |
|          |                          |                        |                |

Notes: Enclosure weight .63 lbs / 286 gm  
 1) Enclosure meets or exceeds IP40 and NEMA 1  
 2) When used with PS19 the enclosure meets or exceeds IP 66 and NEMA 4X, 12 and 13 MIL-STD-810G 506.5  
 3) Circuit Board drawings can be download at:  
[http://www.serpac.com/Products/Sseries/x9x/drawings/09X\\_top-CB.pdf](http://www.serpac.com/Products/Sseries/x9x/drawings/09X_top-CB.pdf)  
 4) All components are RoHS Compliant.

ALL DIMENSIONS ARE ±.010" 3/23/10 (1 of 2)  
 619 Commercial Ave. Covina, CA 91723  
 Ph. (626) 331-0517 Fx. (626) 331-8584 serpac.com

# SERPAC 191 (user print)

Electronic Enclosures



| PART NO. | DESCRIPTION (Included)   | ACCESSORIES (Optional) |                |
|----------|--------------------------|------------------------|----------------|
| 9-1      | TOP                      | PART NO.               | DESCRIPTION    |
| 19       | BOTTOM                   | 50                     | Non-skid Feet  |
| 6005     | #4X3/8" Self tapping (6) | PS19                   | Perimeter Seal |
|          |                          |                        |                |
|          |                          |                        |                |

Notes: Enclosure weight .63 lbs / 286 gm  
 1) Enclosure meets or exceeds IP40 and NEMA 1  
 2) When used with PS19 the enclosure meets or exceeds IP 66 and NEMA 4X, 12 and 13 MIL-STD-810G 506.5  
 3) Circuit Board drawings can be download at:  
[http://www.serpac.com/Products/Sseries/x9x/drawings/09X\\_top-CB.pdf](http://www.serpac.com/Products/Sseries/x9x/drawings/09X_top-CB.pdf)  
 4) All components are RoHS Compliant.

ALL DIMENSIONS ARE  $\pm .010"$  3/23/10 (2 of 2)  
 619 Commercial Ave. Covina, CA 91723  
 Ph. (626) 331-0517 Fx. (626) 331-8584 [www.serpac.com](http://www.serpac.com)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

SERPAC:

[191-GRAY](#) [191-ALMOND](#) [191-BLACK](#)