





SERPAC I152HS

Electronic Enclosures



2 Mounting Brackets included, see sheet 2 for dimensions and for optional mounting Corner Feet and Brackets.

- UL listed to UL 508A 4/4X standard (UL file E519183).
- Material: UV stabilized Polycarbonate Flammability V0, F1 rated material.
- Watertight enclosure meets or exceed Nema 4 and or IP67.


PARTS INCLUDED		
P/N	Qty.	Description
I152HST	1	I152 Hinge Screws Top
I150HSB	1	I150 Hinge Screws Bottom
8150	1	150 O-Ring
1305	2	Mounting Bracket
6028	4	SS #10 X 5/8" Pan H/L
6031	2	#10-32 X 1" Screw
6104	2	10-32 Threaded inserts
8001	2	O-Ring for Screw

Aluminum and Plastic Panel Kits are available as options, see sheets 3-6. The aluminum panel options are: Bottom Panel Kit p/n 7100B Top Panel Kit p/n 7100T Hinged Top Panel Kit p/n 7100TH The plastic panel option is: Hinged Panel Kit p/n 7100HP

SERPAC

Electronic Enclosures

I152 Mounting Bracket Dimensions



INCLUDED STANDARD
1305 FLANGE KIT

Parts included with kit number 1305		
P/N	Qty.	Description
1305	2	Mounting Bracket
6028	4	SS #10 X 5/8" Pan Combo H/L Screw



TOP REMOVED FOR
CLARITY FROM ALL VIEWS

OPTIONAL 1306 CORNER FEET KIT

Part included with kit number 1306		
P/N	Qty.	Description
1306	4	Mounting Corner Feet
6028	4	SS #10 X 5/8" Pan Combo H/L Screw




OPTIONAL 1355 CORNER BRACKETS KIT

Parts included with kit number 1355		
P/N	Qty.	Description
1355	4	Mounting Corner Bracket
6028	4	SS #10 X 5/8" Pan Combo H/L Screw



SERPAC
Electronic Enclosures

7100T Aluminum Top Panel Kit for
I152HL and I152HS






PARTS INCLUDED IN KIT pn 7100T		
P/N	Qty.	Description
71040	1	Aluminum Top Panel
6029	4	SS #10 X 3/8" Pan HL Screw



SERPAC
Electronic Enclosures



7100B Aluminum Bottom Panel Kit for
I152HL and I152HS




PARTS INCLUDED IN KIT 7100B		
P/N	Qty.	Description
71000	1	Aluminum Bottom Panel
6029	4	SS #10 X 3/8" Pan HL Screw



7100TH Aluminum Hinged Top Panel Kit for I152HL and I152HS



OPTIONAL KIT
pn 7100TH







PARTS INCLUDED IN KIT pn 7100TH		
P/N	Qty.	Description
71020	1	Aluminum Hinged Top Panel
6029	2	SS #10 X 3/8" Pan HL Screw
6030	2	SS #10-32 X 3/8" Pan Combo Screw HL Screw
6105	2	SS #10-32 X1/8" Nut
6028	2	SS #10 X 5/8" Pan Combo HL Screw
1307	2	Hinge Pin
1308	1	Panel Hinge A
1309	1	Panel Hinge B



SERPAC


Electronic Enclosures

7100HP Plastic Hinged Top Panel Kit for 152HL and 152HS



PART INCLUDED IN KIT pn 7100HP		
P/N	Qty.	Description
71021	1	Plastic Hinged Top Panel
1310	1	Hinge - Left
1311	1	Hinge - Right
6028	4	SS #10 X 5/8" Pan Combo H/L Screw

71021 Plastic Hinged Top Panel 152HL and 152HS



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

SERPAC:

I152HS- TCBG I152HS-TGBG