





**SERPAC** I352HL  
Electronic Enclosures



2 Mounting Brackets included, see sheet 2 for dimensions and for optional mounting Corner Feet and Brackets.



Aluminum and Plastic Panel Kits are available as options, see sheets 3-6. The aluminum panel options are:  
Bottom Panel Kit p/n 7200B  
Top Panel Kit p/n 7200T  
Hinged Top Panel Kit p/n 7200TH  
The plastic panel option is:  
Hinged Panel Kit p/n 7200HP


- UL listed to UL 508A 4/4X standard (UL file E519183).
- Material: UV stabilized Polycarbonate Flammability V0, F1 rated material.
- Watertight enclosure meets or exceed Nema 4 and or IP67.

| PARTS INCLUDED |      |                                |
|----------------|------|--------------------------------|
| P/N            | Qty. | Description                    |
| I352 HLT       | 1    | I352 Hinged Latch Top          |
| I350 HLB       | 1    | I350 Hinge Latch Bottom        |
| 8350           | 1    | 350 Perimeter O-ring           |
| 7011PCM        | 2    | Safety Latch for I-series (PC) |
| 1305           | 2    | Mounting Bracket               |
| 6028           | 4    | SS #10 X 5/8" Pan H/L          |

4/13/2021

2009 Wright Ave. La Verne, CA 91750  
Ph. (626) 331-0517 Fx. (626) 331-8584 [serpac.com](http://serpac.com)

# I352/I342 Mounting Bracket Dimensions




## INCLUDED STANDARD 1305 FLANGE KIT

| Part included with Kit number 1305 |      |                                   |
|------------------------------------|------|-----------------------------------|
| P/N                                | Qty. | Description                       |
| 1305                               | 2    | Flange                            |
| 6028                               | 4    | SS #10 X 5/8" Pan Combo H/L Screw |

TOP & LATCHES REMOVED FOR CLARITY FROM ALL VIEWS


## OPTIONAL 1306 CORNER FEET KIT

| Part included with Kit number 1306 |      |                                   |
|------------------------------------|------|-----------------------------------|
| P/N                                | Qty. | Description                       |
| 1306                               | 4    | Mounting Corner Foot              |
| 6028                               | 4    | SS #10 X 5/8" Pan Combo H/L Screw |






## OPTIONAL 1355 CORNER BRACKETS KIT

| Part included with Kit number 1355 |      |                                   |
|------------------------------------|------|-----------------------------------|
| P/N                                | Qty. | Description                       |
| 1355                               | 4    | Mounting Corner Bracket           |
| 6028                               | 4    | SS #10 X 5/8" Pan Combo H/L Screw |



# 7200T Aluminum Top Panel Kit for 352HL, 342HL, 352HS, 342HS, 352S and 342S




| Part included in Kit number 7200T |      |                            |
|-----------------------------------|------|----------------------------|
| P/N                               | Qty. | Description                |
| 72040                             | 1    | Top Aluminum Panel         |
| 6029                              | 4    | SS #10 X 3/8" Pan HL Screw |



# 72040 Aluminum Top Panel




## 352HL, 342HL, 352HS, 342HS, 352S and 342S



SERPAC

Electronic Enclosures


7200B Aluminum Bottom Panel Kit for  
352HL, 342HL, 352HS, 342HS, 352S and 342S



| Part included in Kit number 7200B |      |                            |
|-----------------------------------|------|----------------------------|
| P/N                               | Qty. | Description                |
| 72000                             | 1    | Bottom Aluminum Panel      |
| 6029                              | 4    | SS #10 X 3/8" Pan HL Screw |



# 72000 Aluminum Bottom Panel

## 352HL, 342HL, 352HS, 342HS, 352S and 342S






# 7200TH Aluminum Hinged Top Panel Kit for 352HL, 342HL, 352HS, 342HS, 352S and 342S






| Part included in Kit number 7200TH |      |                                    |
|------------------------------------|------|------------------------------------|
| P/N                                | Qty. | Description                        |
| 72020                              | 1    | Aluminum Hinged Top Panel          |
| 6029                               | 2    | SS #10 X 3/8" Pan H/L Screw        |
| 6030                               | 2    | SS #10-32 X 3/8" PH-PN Combo Screw |
| 6105                               | 2    | SS #10-32 Hex Nut Plain            |
| 6028                               | 2    | SS #10 X 5/8" Pan H/L Screw        |
| 1307                               | 2    | Hinge Pin                          |
| 1308                               | 1    | Panel Hinge A                      |
| 1309                               | 1    | Panel Hinge B                      |






# 7200HP Plastic Hinged Top Panel Kit for 352HL, 342HL, 352HS, 342HS, 352S and 342S






Optional kit  
pn 7200HP



| Parts Included in kit number 7200HP |      |                             |
|-------------------------------------|------|-----------------------------|
| P/N                                 | Qty. | Description                 |
| 72021                               | 1    | Plastic Hinged Top Panel    |
| 1310                                | 1    | Panel Hinge Left            |
| 1311                                | 1    | Panel Hinge Right           |
| 6028                                | 4    | SS #10 X 5/8" Pan H/L Screw |

# 72021 Plastic Hinged Top Panel

## 352HL, 342HL, 352HS, 342HS, 352S and 342S



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

SERPAC:

[I352HL, TCBC](#) [I352HL, TGBC](#) [I352HL, TGBG](#)