





SERPAC I632HL


Electronic Enclosures



SERPAC

Electronic Enclosures

I632HL Mounting Bracket Dimensions




INCLUDED STANDARD  
1355 FLANGE KIT

| Parts Included in kit number 1355 |      |                                   |
|-----------------------------------|------|-----------------------------------|
| P/N                               | Qty. | Description                       |
| 1355                              | 4    | Mounting Corner Bracket           |
| 6028                              | 4    | SS #10 X 5/8" Pan Combo H/L Screw |



OPTIONAL 1306 CORNER FEET KIT

| Parts Included in kit number 1306 |      |                                   |
|-----------------------------------|------|-----------------------------------|
| P/N                               | Qty. | Description                       |
| 1306                              | 4    | Mounting Corner Feet              |
| 6028                              | 4    | SS #10 X 5/8" Pan Combo H/L Screw |




SERPAC  
Electronic Enclosures

7300T Aluminum Top Panel Kit for  
I602HL, I622HL, I632 and I652



| Parts Included in kit number 7300T |      |                            |
|------------------------------------|------|----------------------------|
| P/N                                | Qty. | Description                |
| 73040                              | 1    | Aluminum Top Panel         |
| 6029                               | 4    | SS #10 X 3/8" Pan HL Screw |



# 73040 Aluminum Top Panel for I602HL, I622HL, I632 and I652



SERPAC


Electronic Enclosures

7300B Aluminum Bottom Panel Kit for I602HL, I622HL, I632 and I652



| Parts Included in kit number 7300B |      |                            |
|------------------------------------|------|----------------------------|
| P/N                                | Qty. | Description                |
| 73000                              | 1    | Aluminum Bottom Panel      |
| 6029                               | 9    | SS #10 X 3/8" Pan HL Screw |



# 73000 Aluminum Bottom Panel for I602HL, I622HL, I632 and I652



SERPAC

Electronic Enclosures


7300TH Aluminum Hinged Top Panel Kit for I602HL, I622HL, I632 and I652



Optional kit  
pn 7300TH

| Parts Included in kit number 7300TH |      |                                   |
|-------------------------------------|------|-----------------------------------|
| P/N                                 | Qty. | Description                       |
| 73020                               | 1    | Aluminum Hinged Top Panel         |
| 6029                                | 2    | SS #10 X 3/8" Pan HL Screw        |
| 6030                                | 2    | SS #10 X 3/8" Pan Combo H/L Screw |
| 6105                                | 2    | SS #10-32 X1/8" Nut               |
| 6028                                | 2    | SS #10 X 5/8" PH HD H/L Screw     |
| 1307                                | 2    | Hinge Pin for Hinge Panel         |
| 1308                                | 1    | Hinge A for Hinge Panel           |
| 1309                                | 1    | Hinge B for Hinge Panel           |

# 73020 Aluminum Hinged Panel for I602HL, I622HL, I632 and I652



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

SERPAC:

[I632HLCG](#) [I632HLCR](#) [I632HLGG](#) [I632HLRR](#)